

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT - By TE Connectivity

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

P

LTR

DESCRIPTION

DATE

DWN

APVD

E1

REVISED PER ECO-11-005140

06MAY11

RK

HMR

G

1.CHANGE TE LOGO2.ADD LINE IDENTIFICATIONS.TERMINALS TOLERANCE CLARIFICATION ECO-12-005305

02-APR-12

YS.H

BH.Y

Ⓔ NOTE:

1.TERMINAL DIMENSIONS WITHOUT TINNING.

2.LOT NO. SYSTEM AS FOLLOWING:



WEEK


YEAR

3.FOR THE TIN-PLATING OF THE PINS:


+0.1mm FOR WIDTH, THICKNESS AND DIAMETER

+0.5mm FOR LENGTH

CONNECTION DIAGRAM(BOTTOM VIEW)



DRILLING DIAGRAM(BOTTOM VIEW)



TOLERANCE

Diagram dimension	Tolerance
max. 1mm	±0.1mm
1 - 3mm	±0.2mm
min. 3mm	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

H.SASAKI

CHK

Y.OIKAWA

APVD

A.NAGAI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

FINISH

TE

TE Connectivity

NAME

OSA-SH-DM5,000 ,000M

SIZE

CAGE CODE

DRAWING NO

3-1419124-9

RESTRICTED TO

A300779

C=

3-1419124-9

SCALE


4:1

SHEET

1 OF 2

REV

G



0.90

0.90

24.80 ±0.5

4 ±0.5

LOT NO. Ⓔ

ONE CHARACTER FOR LINE IDENTIFICATION Ⓔ

MADE IN CHINA

TV-3

5A 240V~

5A 30V~



4A/65A 250V~

4A/65A 250V~
5A 250V~

OEG



0.45

0.30

0.50

7.50 ±0.2

7.50 ±0.2

12.90 ±0.5

15 ±0.2

5 ±0.2

2.45

24.40 ±0.5