



2.5 x 2.0 x 0.9mm

ASTX-H12



ESD Sensitive



RoHS/RoHS II compliant

Moisture Sensitivity Level (MSL)–1

FEATURES:

- HCMOS Output
- Compact and low in height
- Low current consumption; IR reflow possible
- Suitable for high-density SMT

APPLICATIONS:

- Cellular and cordless phones
- Standard OSC for exact equipment
- Mobile communication equipment
- Portable radio equipment and music player

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		3.200		55.000	MHz	
Standard Frequencies		5, 10, 12, 16, 20, 24, 32, 40, 44			MHz	
Operating Temperature		-30		+75	°C	
Storage Temperature:		-40		+125	°C	
Frequency Stability $\Delta f/f_0$ vs Tolerance (@+25°C)		-2.0		+2.0	ppm	1 hr after reflow
vs Temperature (ref. to +25°C)		-2.5		+2.5		See option (Table 1)
vs Supply Voltage Change (Vdd $\pm$ 5%)		-0.2		+0.2		
vs Load Change (ZL $\pm$ 10%)		-0.2		+0.2		
vs Aging (first year @+25°C)		-1.0		+1.0		
Supply Voltage (Vdd)		+2.97	+3.3	+3.63	V	See option
Supply Current (Icc)				4.0	mA	4~10MHz
				4.8		~20MHz
				5.5		~30MHz
				6.0		~40MHz
				7.0		~54MHz
Rise and Fall Time (Tr/Tf)				5	ns	10%-90%Vdd
Symmetry		45		55		@1/2 Vdd
Output Voltage	V _{OH}	90%Vdd			V	
	V _{OL}			10%Vdd		
Load				15	pF	
Waveform		HCMOS				
Phase Noise (Frequency dependant)			-130		dBc	@1kHz offset
			-158			@100kHz offset
Tri-state Function (Stand-by) :		"1" (VIH $\geq$ 0.75*Vdd) or Open: Oscillation "0" (VIL<0.25*Vdd) : Hi Z			V	



2.5 x 2.0 x 0.9mm

ASTX-H12



RoHS/RoHS II compliant

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

ASTX-H12- - MHz - -

Vdd (V)
Blank: 3.3V±10%
A: 2.8V±10%
B: 2.5V±10%


Frequency in MHz
Please specify the frequency in MHz. e.g. 19.200MHz

Packaging
Blank: Bulk
T: 1000pcs/reel


	±2.5ppm	±3.0ppm	±4ppm	±5ppm
0°C ~ +50°C	D25	D30	D40	D50
-10°C ~ +60°C	E25	E30	E40	E50
-0°C ~ +70°C	F25	F30	F40	F50
-20°C ~ +75°C	G25	G30	G40	G50
-30°C ~ +75°C	Blank(STD)	H30	H40	H50
-40°C ~ +85°C	I25	I30	I40	I50

Table 1

OUTLINE DIMENSIONS:



Recommended Land Pattern




Tri-state pin	Output
High or floating	Active
Low	Hi-impedance

Note: Recommend using an approximately 0.01μF bypass capacitor between Pin 2 and 4.

PIN	FUNCTION
1	Tri-state
2	GND
3	Output
4	Vdd


Dimensions: mm

REFLOW PROFILE:



TAPE & REEL:

T: 1,000pcs/reel



Dimensions: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASTX-H12-10.000Z-I25-T](#) [ASTX-H12-10.000Z-T](#) [ASTX-H12-12.000Z-I25-T](#) [ASTX-H12-12.000Z-T](#) [ASTX-H12-13.000Z-I25-T](#) [ASTX-H12-13.000Z-T](#) [ASTX-H12-16.000Z-I25-T](#) [ASTX-H12-16.000Z-T](#) [ASTX-H12-19.200Z-I25-T](#) [ASTX-H12-19.200Z-T](#) [ASTX-H12-19.680Z-I25-T](#) [ASTX-H12-19.680Z-T](#) [ASTX-H12-20.000Z-I25-T](#) [ASTX-H12-20.000Z-T](#) [ASTX-H12-24.000Z-I25-T](#) [ASTX-H12-24.000Z-T](#) [ASTX-H12-26.000Z-I25-T](#) [ASTX-H12-26.000Z-T](#) [ASTX-H12-32.000Z-I25-T](#) [ASTX-H12-32.000Z-T](#) [ASTX-H12-40.000Z-I25-T](#) [ASTX-H12-40.000Z-T](#) [ASTX-H12-44.000Z-I25-T](#) [ASTX-H12-44.000Z-T](#) [ASTX-H12-5.000Z-I25-T](#) [ASTX-H12-5.000Z-T](#) [ASTX-H12-B-10.000Z-I25-T](#) [ASTX-H12-B-10.000Z-T](#) [ASTX-H12-B-12.000Z-I25-T](#) [ASTX-H12-B-12.000Z-T](#) [ASTX-H12-B-13.000Z-I25-T](#) [ASTX-H12-B-13.000Z-T](#) [ASTX-H12-B-16.000Z-I25-T](#) [ASTX-H12-B-16.000Z-T](#) [ASTX-H12-B-19.200Z-I25-T](#) [ASTX-H12-B-19.200Z-T](#) [ASTX-H12-B-19.680Z-I25-T](#) [ASTX-H12-B-19.680Z-T](#) [ASTX-H12-B-20.000Z-I25-T](#) [ASTX-H12-B-20.000Z-T](#) [ASTX-H12-B-24.000Z-I25-T](#) [ASTX-H12-B-24.000Z-T](#) [ASTX-H12-B-26.000Z-I25-T](#) [ASTX-H12-B-26.000Z-T](#) [ASTX-H12-B-32.000Z-I25-T](#) [ASTX-H12-B-32.000Z-T](#) [ASTX-H12-B-40.000Z-I25-T](#) [ASTX-H12-B-40.000Z-T](#) [ASTX-H12-B-44.000Z-I25-T](#) [ASTX-H12-B-44.000Z-T](#) [ASTX-H12-B-5.000Z-I25-T](#) [ASTX-H12-B-5.000Z-T](#) [ASTX-H12-10.000MHZ-T](#) [ASTX-H12-12.000MHZ-T](#) [ASTX-H12-20.000MHZ-T](#) [ASTX-H12-40.000MHZ-I25-T](#) [ASTX-H12-25.000MHZ-T](#) [ASTX-H12-22.5792MHZ-T](#) [ASTX-H12-49.152MHZ-T](#) [ASTX-H12-10.000MHZ-I25-T](#) [ASTX-H12-12.000MHZ-I25-T](#) [ASTX-H12-13.000MHZ-I25-T](#) [ASTX-H12-13.000MHZ-T](#) [ASTX-H12-16.000MHZ-I25-T](#) [ASTX-H12-16.000MHZ-T](#) [ASTX-H12-B-40.000MHZ-I25-T](#) [ASTX-H12-B-40.000MHZ-T](#) [ASTX-H12-B-44.000MHZ-I25-T](#) [ASTX-H12-B-44.000MHZ-T](#) [ASTX-H12-B-5.000MHZ-I25-T](#) [ASTX-H12-B-5.000MHZ-T](#) [ASTX-H12-B-24.000MHZ-I25-T](#) [ASTX-H12-B-24.000MHZ-T](#) [ASTX-H12-B-26.000MHZ-I25-T](#) [ASTX-H12-B-26.000MHZ-T](#) [ASTX-H12-B-32.000MHZ-I25-T](#) [ASTX-H12-B-32.000MHZ-T](#) [ASTX-H12-B-19.200MHZ-I25-T](#) [ASTX-H12-B-19.200MHZ-T](#) [ASTX-H12-B-19.680MHZ-I25-T](#) [ASTX-H12-B-19.680MHZ-T](#) [ASTX-H12-B-20.000MHZ-I25-T](#) [ASTX-H12-B-20.000MHZ-T](#) [ASTX-H12-B-12.000MHZ-I25-T](#) [ASTX-H12-B-12.000MHZ-T](#) [ASTX-H12-B-13.000MHZ-I25-T](#) [ASTX-H12-B-13.000MHZ-T](#) [ASTX-H12-B-16.000MHZ-I25-T](#) [ASTX-H12-B-16.000MHZ-T](#) [ASTX-H12-44.000MHZ-I25-T](#) [ASTX-H12-44.000MHZ-T](#) [ASTX-H12-5.000MHZ-I25-T](#) [ASTX-H12-5.000MHZ-T](#) [ASTX-H12-B-10.000MHZ-I25-T](#) [ASTX-H12-B-10.000MHZ-T](#) [ASTX-H12-24.000MHZ-T](#) [ASTX-H12-26.000MHZ-I25-T](#) [ASTX-H12-26.000MHZ-T](#) [ASTX-H12-32.000MHZ-I25-T](#) [ASTX-H12-32.000MHZ-T](#)