


MECHANICAL DATA

Dimensions in mm (inches)



DUAL NPN PLANAR TRANSISTORS IN TO77 PACKAGE

TO-77 PACKAGE

PIN 1 – Collector 1 PIN 4 – Emitter 2
PIN 2 – Base 1 PIN 5 – Base 2
PIN 3 – Emitter 1 PIN 6 – Collector 2

ABSOLUTE MAXIMUM RATINGS

($T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)

			EACH SIDE	TOTAL DEVICE
V_{CBO}	Collector – Base Voltage		45V	
V_{CEO}	Collector – Emitter Voltage ¹		45V	
V_{EBO}	Emitter – Base Voltage		6V	
I_C	Continuous Collector Current		30	
P_D	Total Device Dissipation	$T_{AMB} = 25^{\circ}\text{C}$	300mW	500mW
		Derate above 25°C	1.72mW / $^{\circ}\text{C}$	2.86W / $^{\circ}\text{C}$
P_D	Total Device Dissipation	$T_C = 25^{\circ}\text{C}$	750mW	1.5W
		Derate above 25°C	4.3mW / $^{\circ}\text{C}$	8.6mW / $^{\circ}\text{C}$
T_{STG}	Storage Temperature Range		-65 to 200°C	
T_L	Lead temperature (Soldering, 10 sec.)		300 $^{\circ}\text{C}$	

NOTES

1. Base – Emitter Diode Open Circuited.

ELECTRICAL CHARACTERISTICS ($T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated)

Parameter	Test Conditions ¹	Min.	Typ.	Max.	Unit
INDIVIDUAL TRANSISTOR CHARACTERISTICS					
$V_{(BR)CBO}$ Collector – Base Breakdown Voltage	$I_C = 10\mu\text{A}$ $I_E = 0$	45			V
$V_{(BR)CEO^*}$ Collector – Emitter Breakdown Voltage	$I_C = 10\text{mA}$ $I_B = 0$	45			
$V_{(BR)EBO}$ Emitter – Base Breakdown Voltage	$I_E = 10\mu\text{A}$ $I_C = 0$	6			
I_{CBO} Collector Cut-off Current	$V_{CB} = 45\text{V}$ $I_E = 0$			10	nA
	$T_A = 150^{\circ}\text{C}$			10	μA
I_{CEO} Collector Cut-off Current	$V_{CE} = 5\text{V}$ $I_B = 0$			2	nA
I_{EBO} Emitter Cut-off Current	$V_{EB} = 5\text{V}$ $I_C = 0$			2	
h_{FE} DC Current Gain	$V_{CE} = 5\text{V}$ $I_C = 10\mu\text{A}$	150		600	—
	$T_A = -55^{\circ}\text{C}$	30			
	$V_{CE} = 5\text{V}$ $I_C = 100\mu\text{A}$	225			
	$V_{CE} = 5\text{V}$ $I_C = 1\text{mA}$	300			
V_{BE} Base – Emitter Voltage	$V_{CE} = 5\text{V}$ $I_C = 100\mu\text{A}$			0.70	V
$V_{CE(sat)}$ Collector – Emitter Saturation Voltage	$I_B = 100\mu\text{A}$ $I_C = 1\text{mA}$			0.35	
h_{ib} Small Signal Common – Base Input Impedance	$V_{CB} = 5\text{V}$ $I_C = 1\text{mA}$ $f = 1\text{kHz}$	25		32	Ω
h_{ob} Small Signal Common – Base Output Admittance	$V_{CB} = 5\text{V}$ $I_C = 1\text{mA}$ $f = 1\text{kHz}$			1	μmho
$ h_{fe} $ Small Signal Common – Base Current Gain	$V_{CE} = 5\text{V}$ $I_C = 500\mu\text{A}$ $f = 20\text{MHz}$	3			—
C_{obo} Common – Base Open Circuit Output Capacitance	$V_{CB} = 5\text{V}$ $I_E = 0$ $f = 140\text{kHz to } 1\text{MHz}$			6	pF

* Pulse Test: $t_p = 300\mu\text{s}$, $\delta \leq 1\%$.

Parameter	Test Conditions	2N2916		2N2918		Unit
		Min.	Typ. Max.	Min.	Typ. Max.	
TRANSISTOR MATCHING CHARACTERISTICS						
h_{FE1}	Static Forward Current	$V_{CE} = 5V$	$I_C = 100\mu A$	0.9	1	—
h_{FE2}	Gain Balance Ratio	See Note 2.				
$ V_{BE1} - V_{BE2} $	Base – Emitter Voltage	$V_{CE} = 5V$	$I_C = 100\mu A$		3	5
	Differential	$V_{CE} = 5V$	$I_C = 10\mu A$ to 1mA		5	10
$ \Delta(V_{BE1} - V_{BE2})/\Delta T_A $		$V_{CE} = 5V$	$I_C = 100\mu A$			
	Base – Emitter Voltage	$T_{A1} = 25^{\circ}C$	$T_{A2} = -55^{\circ}C$		0.8	1.6
	Differential Change With Temperature	$V_{CE} = 5V$	$I_C = 100\mu A$		1	2
		$T_{A1} = 25^{\circ}C$	$T_{A2} = 125^{\circ}C$			

NOTES

- 1) Terminals not under test are open circuited under all test conditions.
- 2) The lower of the two readings is taken as h_{FE1} .