



Home > Products > Stainless Steel Media Isolated > AB/HP > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

ABH03KPSC1B



AB/HP Series Flush Mount Pressure Sensor, Unamplified, Sealed Gage, 0 psi to 3,000 psi, Item Number 9222506

Actual product appearance may vary.

Features

- Flush-mount option
- To 0.25% accuracy
- Wide choice of pressure ranges available
- 0 psi to 6 psi with ranges through 0 psi to 10,000 psi
- Adaptable design
- PSIA models
- For critical applications
- Installed in customer fixtures
- Applicable to special packaging
- Wide range of applications
- Measures in vacuum region

Potential Applications

- Liquid-level measurement
- Landing gear hydraulic pressure
- Vehicle braking systems
- Physiological monitors
- Geophysical research
- Engine monitor control

Description

The AB-High Performance pressure transducer is extremely accurate down to 0.25% span over a wide compensated temperature range. Both zero and full-scale temperature compensation are held to extremely narrow limits.

The transducer's body is made in a configuration permitting its use as a 'flush mounted' device in situations where ease of cleaning or low-fluid volumes are major requirements. It may also be mounted in an adapter for more conventional installations. Made from 316L or 155PH stainless steel, the AB/HP offers premium performance and flexibility at OEM prices.

Supporting Documentation

 [Dimensions and Circuity](#)

 [Documentation](#)

Product Specifications	
Measurement Type	Sealed Gage
Signal Conditioning	Unamplified
Pressure Range	0 psi to 3,000 psi
Supply Voltage	5.0 Vdc, 6.0 Vdc max.
Maximum Overpressure	6,000 psi
Burst Pressure	15,000 psi
Port Style	Flush Diaphragm
Temperature Compensation	Yes
Output Type	0 mV to 100 mV
Accuracy	0.25% full scale BFSL
Response Time	less than 0.5 ms
Input Impedance	150 ohms \pm 50 ohms
Output Impedance	115 ohms \pm 25 ohms
Insulation Resistance	1000 Mohms @ 50 Vdc max.
Output Calibration	Yes
Termination Type	0.91 m [3 ft] 4 - Conductor Shielded Cable
Weight	57 grams [2.0 ounces]
Full Scale Span	100 mV \pm 1 mV
Operating Temperature Range	-54 °C to 93 °C [-65 °F to 200 °F]
Compensated Temperature Range	-1 °C to 71 °C [30 °F to 160 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack 15 -5PH stainless steel
Approvals	CE
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	AB/HP

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.

Product Search

Part number search:

Use (*) to expand search

Specification Search