

## High Surge Current Two-pin *SIDACtor*® Device



This *SIDACtor* device is intended for very hostile environments such as CATV (Community Antenna TV) systems and electronics connected to external antennas.

### Electrical Parameters

| Part Number *   | V <sub>DRM</sub><br>Volts | V <sub>S</sub><br>Volts | V <sub>T</sub><br>Volts | I <sub>DRM</sub><br>μAmps | I <sub>S</sub><br>mAmps | I <sub>T</sub><br>Amps | I <sub>H</sub><br>mAmps |
|-----------------|---------------------------|-------------------------|-------------------------|---------------------------|-------------------------|------------------------|-------------------------|
| <b>P1400ADL</b> | 120                       | 160                     | 3                       | 5                         | 800                     | 2.2                    | 50                      |
| <b>P1800ADL</b> | 170                       | 220                     | 3                       | 5                         | 800                     | 2.2                    | 50                      |

\* "L" in part number indicates RoHS compliance. For non-RoHS compliant device, delete "L" from part number.  
For surge ratings, see table below.

#### General Notes:

- All measurements are made at an ambient temperature of 25 °C. I<sub>PP</sub> applies to -40 °C through +85 °C temperature range.
- I<sub>PP</sub> is a repetitive surge rating and is guaranteed for the life of the product.
- Listed *SIDACtor* devices are bi-directional. All electrical parameters and surge ratings apply to forward and reverse polarities.
- V<sub>DRM</sub> is measured at I<sub>DRM</sub>.
- V<sub>S</sub> is measured at 100 V/μs.
- Special voltage (V<sub>S</sub> and V<sub>DRM</sub>) and holding current (I<sub>H</sub>) requirements are available upon request.

### Surge Ratings in Amps


| Series | I <sub>PP</sub>     |                         | I <sub>TSM</sub><br>50 / 60 Hz<br>Amps | di/dt<br>Amps/μs |
|--------|---------------------|-------------------------|----------------------------------------|------------------|
|        | 8x20 *<br>1.2x50 ** | 10x1000 *<br>10x1000 ** |                                        |                  |
|        | Amps                | Amps                    |                                        |                  |
| D      | 1000                | 250                     | 120                                    | 500              |

\* Current waveform in μs

\*\* Voltage waveform in μs

SIDACtor Devices


### Thermal Considerations

| Package                                                                                              | Symbol          | Parameter                               | Value       | Unit |
|------------------------------------------------------------------------------------------------------|-----------------|-----------------------------------------|-------------|------|
| <br>Modified TO-220 | $T_J$           | Operating Junction Temperature Range    | -40 to +150 | °C   |
|                                                                                                      | $T_S$           | Storage Temperature Range               | -65 to +150 | °C   |
|                                                                                                      | $R_{\theta JA}$ | Thermal Resistance: Junction to Ambient | 60          | °C/W |




### Capacitance Values

| Part Number | pF  |     |
|-------------|-----|-----|
|             | MIN | MAX |
| P1400ADL    | 140 | 200 |
| P1800ADL    | 120 | 180 |

Note: Off-state capacitance ( $C_O$ ) is measured at 1 MHz with a 2 V bias.



V-I Characteristics


 $t_r \times t_d$  Pulse Waveform

Normalized  $V_S$  Change versus Junction Temperature


Normalized DC Holding Current versus Case Temperature