






LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO-12-013349	20JUL12	PY	RG



PANEL CUTOUT



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM MATING FACE OF CONNECTOR

1. UNLESS OTHERWISE SPECIFIED DIMENSIONS TOLERANCE ARE ± 0.2
2. DWV RATING: 875VAC @ SEA LEVEL
3. WORKING TEMPERATURE: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK
O RING : SILICONE RUBBER

5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

6. WATER PROOF: 1M IMMERSION
7. WIRE SIZE: 28 AWG MAX.

8 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT I.D.

2	CHROMIUM-BLACK	DOUBLE	PCB	2157952-1
SHELL SIZE	FINISH	POLARIZATION	TERMINATION	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C THOMAS 10APR2012	TE Connectivity		
DIMENSIONS: mm		CHK R. GROSS 10APR2012			
		APVD R. GROSS 10APR2012	NAME		
		PRODUCT SPEC 108-127005	CIRCULAR HD RECEPTACLE WITH SOLDER CUP SOCKETS CONTACTS - 9 POS		
MATERIAL		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=2157952
FINISH		WEIGHT -	RESTRICTED TO -		SCALE NTS
CUSTOMER DRAWING		SHEET 1 of 1		REV B	