



- NOTES:
1. MATERIALS AND FINISHES:
BODIES - STAINLESS STEEL, PASSIVATED
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 4 GHz
C. RETURN LOSS: 30 dB MIN @ 3 GHz
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, APH-NP-HDBNCJ, AND DATE CODE"

THIRD ANGLE PROJ.		REVISIONS			
REV	DESCRIPTION	DATE	ECO	APPR	
A	RELEASE TO MFG	14-Oct-10	48270	TD	



SCALE 2.000

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ± 0.3mm ANGLES ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN	DATE	TITLE		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
	SEE NOTES	T.DENG	14-Oct-10				
	REFERENCE	ENGINEER	DATE	ADAPTOR, 75 OHM N PLUG TO HD BNC JACK		DRAWING NO. APH-NP-HDBNCJ	
	EAR #4100	KARTHIK R	22-Mar-10			ITEM NO. APH-NP-HDBNCJ	
	CONFIGURATION LEVEL: Prototype	APPROVED	DATE	SCALE: 5.0:1.0	SHEET 2 OF 2	PART NO. APH-NP-HDBNCJ	
	FINISH	CAD FILE		DWG SIZE	REV		
		Root Folder/HD-BNC/APH-NP-HDBNCJ		B	A		