



PRODUCT NO. NOTE ①		DIM L	DIM S
72336-100CA	72336-100CALF	0	13
72336-122CA	72336-122CALF	2.2	
72336-143CA	72336-143CALF	4.3	
72336-150CA	72336-150CALF	5	
72336-100DA	72336-100DALF	0	15.6
72336-122DA	72336-122DALF	2.2	
72336-143DA	72336-143DALF	4.3	
72336-150DA	72336-150DALF	5	
72336-100FA	72336-100FALF	0	21
72336-122FA	72336-122FALF	2.2	
72336-143FA	72336-143FALF	4.3	
72336-150FA	72336-150FALF	5	




NOTES:

- ① ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (2 PER ASSEMBLY).



2. LINK TO MOVE ALONG INSIDE WALL OF COVER PLATE SMOOTHLY AFTER ASSEMBLING WITH HEADER.
3. MATERIAL:
PLASTIC GUIDES: POLYPHTHARAMIDE UL94V-0
COLOR: BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
4. FINISH:
EMI CONTACT: CONTACT AREA: 0.5um Au
UNDER PLATING: 2.0um Ni
5. RECOMMENDED SCREW TORQUE:
1.0-1.5 MAX IN-LBS(1.2-1.7 CM-KGS)




mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		PCMCIA
ltr	ecm no	dr	date	tolerances unless otherwise specified			title
C	T70090	RHG	4/28/97	angles	.X±.3	MM	NARROW BODY FRONT EJECT
D	V12231	TFG	9/19/01	linear	.XX±.13		CARDBUS MECHANISM ASSEMBLY
E	N06-0188	MZ	07/12/06	±2'	.XXX±.051	scale	
F	N08-0060	MZ	6/20/08	dr	Mike Zhou	07/11/06	dwg no
				enr	Mike Zhou	07/11/06	sheet 1 of 3 size
				chr	Qin David	07/11/06	72336 A4
				appd	Jack Wang	07/11/06	type CUSTOMER Drawing
sheet	revision	F	F	F			
index	sheet	1	2	3			



PRODUCT NO. NOTE ①		DIM L	DIM S
72336-000CA	72336-000CALF	0	13
72336-022CA	72336-022CALF	2.2	
72336-043CA	72336-043CALF	4.3	
72336-050CA	72336-050CALF	5	
72336-000DA	72336-000DALF	0	15.6
72336-022DA	72336-022DALF	2.2	
72336-043DA	72336-043DALF	4.3	
72336-050DA	72336-050DALF	5	
72336-000FA	72336-000FALF	0	21
72336-022FA	72336-022FALF	2.2	
72336-043FA	72336-043FALF	4.3	
72336-050FA	72336-050FALF	5	

NOTES:

- ① ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (2 PER ASSEMBLY).




2. LINK TO MOVE ALONG INSIDE WALL OF COVER PLATE SMOOTHLY AFTER ASSEMBLING WITH HEADER.
3. MATERIAL:
PLASTIC GUIDES: POLYPHTHARAMIDE UL94V-0
COLOR: BLACK
COVER PLATE: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
4. FINISH:
EMI CONTACT: CONTACT AREA: 0.5um Au
UNDER PLATING: 2.0um Ni
5. RECOMMENDED SCREW TORQUE:
1.0-1.5 MAX IN-LBS(1.2-1.7 CM-KGS)



mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family PCMCIA			
ltr	ecm no	dr	date	tolerances unless otherwise specified			title			
F				angles	linear	.X±.3 .XX±.13 .XXX±.051	NARROW BODY FRONT EJECT CARDBUS MECHANISM ASSEMBLY			
				±2'		scale	dwg no			
				dr	Mike Zhou	07/11/06	sheet 2 of 3 size			
				enr	Mike Zhou	07/11/06	72336			
				chr	Qin David	07/11/06	A4			
				appd	Jack Wang	07/11/06	type CUSTOMER Drawing			
sheet	revision									
index	sheet									

NOTE ①	PRODUCT NO.	③ STAND-OFF PART NUM.	DIM L	DIM S	④ BUTTON PART NUM.	DIM M
72336-101CA	72336-100CALF	NONE	0	28.0	52211-002	103.05
72336-151CA	72336-150CALF	92706-005	5			




TO BE PRESS-FITTED INTO THE HOLE OF GUIDE.

VIEW X

NOTES:

- ① ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (2 PER ASSEMBLY).




PART NO.	STAND-OFF
93925-001	0mm
93925-002	2.2mm
93925-003	4.3mm
93925-004	5mm

2. PACKAGING SPECIFICATION: GS-14-382

①	RIVET	61723-002	1
②	HOLD-DOWN	SEE NOTE 1	2
③	STAND-OFF	SEE TABLE ABOVE	2
④	BUTTON	SEE TABLE ABOVE	1
⑤	LINK ARM	72227-001	1
⑥	PUSH ROD	95081-001	1
⑦	CLIP RIGHT	94836-110M	1
⑧	CLIP LEFT	94837-110M	1
⑨	RIGHT GUIDE	71731-002	1
⑩	LEFT GUIDE	71730-001	1
⑪	COVER PLATE	72228-001	1
No.	DESCRIPTION	P/N	Q'TY

72336-1XXXX



mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		PCMCIA
ltr	ecn no	dr	date	title
F				NARROW BODY FRONT EJECT
				CARDBUS MECHANISM ASSEMBLY
				dwg no
				72336
				sheet 3 of 3 size
				A4
				type
				CUSTOMER
				Drawing
sheet	revision			
index	sheet			