


T/C CHARACTERISTICS (SEE NOTE 2)	
% OF RATING	CLEARING TIME
100%	4 HOURS, MINIMUM
135%	1 HOUR, MAXIMUM
200%	5 SEC. MIN. 60 SEC. MAX.



NOMINAL LENGTH 31.75 [1.25]

1. FUSES ARE LISTED BY UNDERWRITERS' LABORATORIES.
2. IN ACCORDANCE WITH UNDERWRITERS' LABORATORIES STANDARD U.L. 248-14.
3. PARTS ARE BOTH Pb FREE AND RoHS COMPLIANT.
4. LEAD WIRE ARE TIN PLATED.
5. FOR RoHS REPORTING DOCUMENTS SEE ES-001156.

NO	COMPONENT NO	DESCRIPTION	QTY /M	U /M
BILL OF MATERIAL				
A	LTR	COPIES TO 1 9 18 2 10 19 3 12 20 4 13 21 5 14 23 6 15 33 7 16 43 8 17 53 3RD ANGLE PROJECTION 		
	MATL SPEC FINISH DRW RP DATE 4 / 16 / 08 SCALE 2 : 1 CHK DATE SUPER DRW APPD DATE FINISH GOOD WT TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.25[.01] FRACTION ± THREE PLACE DEC ±.100[.004] ANGULAR ±1°			
		TITLE 3AG, SLO-BLO FUSES REVISION DRWG. NO. OUTLINE		
		 DES PLAINES, ILLINOIS 60016 0373000P SERIES		
		CHK	APD	