

## Energy Division

# LC Series Photocontrol Locking Style-Residential Grade

Tyco Electronics LC Series offers a locking style control ideal for residential lighting applications.

### Features

- Heavy-Duty Thermal Bi-Metal Switch
- 30-45 Second Time Delay
- UL Listed
- ANSI C136.10 Compliant
- Fail Mode is ON

### Innovative Design

The LC Series locking-type photocontrol offers an economical and cost-effective means of controlling residential lighting systems from dusk to dawn.

### Key Benefits

A heavy-duty thermal bi-metal switch that produces a minimum 30-45 second time delay, virtually eliminating unwanted off/on operations that could result from lightning, car headlights or other sudden changes in the ambient outdoor light level.


LC controls are a perfect and reliable solution for lighting driveways, patios, decks, entryways or other areas around the home where security lighting is desired.

### Common Uses for the LC Series

- Driveway Lighting
- Patio Lighting
- Deck Lighting
- Entryway Lighting

The LC Series is the result of over fifty years of experience designing and delivering superior photocontrols and other lighting accessories in the US and around the world.

ALR-LC-120



#### Features

Rated Volts	105 - 305 VAC
Frequency	50 - 60 Hz
Operating Light Levels	Standard 1.5 Fc ON
Time Delay	30 - 45 Second Delay ON and OFF
OFF/ON Ratio	4:1
Fail Mode	ON
Rated Life	4 years

#### Specifications


##### Physical

- Dimensions: approx. 2.87" [73mm] dia x 1.61" [41mm] high (LC-120)
- Dimensions: approx. 2.93" [74mm] dia x 1.98" [50mm] high (LC-208-277)
- Enclosure: designed to meet ANSI C136.10
- Power consumption: 0.9 watts (avg.) at 120 VAC
- Minus 40°C to plus 65°C @ 96% RH
- SPST thermal bi-metallic
- Exceeds 5000 on/off operations
- 1000 Watt Tungsten 1800 VA
- High Impact UV stabilized polycarbonate (LC-120), noryl (LC-208-277)
- High temperature polyester (PBT)
- Cross-linked polyethylene
- 3-Pole locking-type with solid brass legs
- 1/2" Cadmium Sulfide (CdS) Cell

Temperature  
Switch  
Control  
Load Rating  
Cover

Base  
Gasket  
Connection  
Light Sensor

ALR-LC-208-277



#### Selection Information

Model	Rated Volts	Range (Volts)	Rating Tungsten (Watts)	Rating Ballast (VA)	Turn On (Fc)	OFF/ON Ratio	POP Pkg.
LC-120	120	105 - 130	1000	1800	1.5	4 : 1	
CPGI-ALR-LC-120	120	105 - 130	1000	1800	1.5	4 : 1	Yes
LC-208-277	208/240/277	185 - 305	1000	1800	1.5	4 : 1	
CPGI-ALR-LC-208-207	208/240/277	185 - 305	1000	1800	1.5	4 : 1	Yes

Tyco Electronics Corporation  
8000 Purfoy Road  
Fuquay Varina, NC 27526-9349  
Tel: 800.327.6996  
Fax: 800.527.8350  
E-mail: [naenergy@tycoelectronics.com](mailto:naenergy@tycoelectronics.com)  
<http://energy.tycoelectronics.com/photocontrols>  
[www.tycoelectronics.com](http://www.tycoelectronics.com)

Copyright 2009 Tyco Electronics Corporation.  
2-1773455-4 E358 01/10

All of the above information, including drawings, illustrations and graphic designs, reflects our present understanding and is to the best of our knowledge and belief correct and reliable. Users, however, should independently evaluate the suitability of each product for the desired application. Under no circumstances does this constitute an assurance of any particular quality or performance. Such an assurance is only provided in the context of our product specifications or explicit contractual arrangements. Our liability for these products is set forth in our standard terms and conditions of sale. TE (logo) and Tyco Electronics are trademarks of the Tyco Electronics group of companies and its licensors. Other products, logos, and Company names mentioned herein may be trademarks of their respective owners.

**Energy Division - A pioneer in the development of economical solutions for the electrical power industry. Our product range includes: cable accessories, connectors & fittings, electrical equipment, instruments, lighting controls, insulators & insulation enhancement and surge arresters.**

Mike O'Toole  
Tyco Electronics, Energy Inside Sales

ALR = Area Lighting Research. The name of the company who made these parts before Tyco purchased them. We keep the ALR as part of the part #'ing for brand recognition.

CPGI prefix designates a clam shell, see-thru package designed to hang on a rod in a retail environment. It also has a std pack qty of 10 pcs.

Non CPGI parts come in a thin cardboard box. You cannot see through it nor hang it but it easily opens for inspection of the part. Std pack qty on these is 12 pcs

The W suffix designates the inclusion of a wall plate. It is pictured above in the CPGI packaging.

Thanks,

Mike O'Toole  
Tyco Electronics, Energy Inside Sales  
michael.otoole@te.com  
Office Phone 1-800-327-6996, Industrial Option Fax 1-800-527-8350