

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2002

© COPYRIGHT 2002

BY -

ALL RIGHTS RESERVED.


4

3

2

1

AGGANCIO SECONDARIO COMPLETAMENTE INSERITO
(SECONDARY LOCK COMPLETELY MOUNTED)



SCALE 3:2


21.0

6.3

5.2

3.8

19.1±0.3



7.3


30.1±0.3

18.7

33.7±0.3

15.0

45.5±0.3



29.40


4.65 PASSO (PITCH)

2.3


4.20 PASSO (PITCH)

5.50 PASSO (PITCH)

48.8±0.4



STATO DI FORNITURA
(SUPPLYING CONDITION)




15.6±0.3

9.5

5.0


11.8

20.8±0.4



2

DISPOSITIVO AGGANCIO SECONDARIO (SECONDARY LOCK)



SCALE 3:2

1) IL CONNETTORE SI ACCOPPIA CON LA CONTROPARTE P/N 284875
(CONNECTOR MATEABLE WITH COUNTERPART P/N 284875)

2) N.RO 4 CAVITA' ADATTE PER CONTATTI MASCHIO 2.8x0.6mm TYP.A STAGNATI
(N. 4 CAVITIES SUITABLE FOR 2.8x0.6mm TYP. A TAB CONTACTS TIN PLATED)
P/N 2-964294-1 : ADATTO PER RANGO FILO 0.5-1.0 sqmm
(SUITABLE FOR 0.5-1.0 sqmm WIRE SECTION)
P/N 2-964296-1 : ADATTO PER RANGO FILO > 1.0-2.5 sqmm
(SUITABLE FOR > 1.0-2.5 sqmm WIRE SECTION)

3) N.RO 16 CAVITA' ADATTE PER CONTATTI MASCHIO 1.6x0.8mm TYP.A STAGNATI
(N. 16 CAVITIES SUITABLE FOR 1.6x0.8mm TYP. A TAB CONTACTS TIN PLATED)
P/N 964265-2 : ADATTO PER RANGO FILO 0.35-0.5 sqmm
(SUITABLE FOR 0.35-0.5 sqmm WIRE SECTION)
P/N 964267-2 : ADATTO PER RANGO FILO > 0.5-1.0 sqmm
(SUITABLE FOR > 0.5-1.0 sqmm WIRE SECTION)
P/N 1241846-2 : ADATTO PER RANGO FILO > 1.0-1.5 sqmm
(SUITABLE FOR > 1.0-1.5 sqmm WIRE SECTION)

4) IL CONNETTORE VIENE FORNITO CON AGGANCIO SECONDARIO NELLA STESSA SCATOLA IN PARI QUANTITA'
(CONNECTOR IS SUPPLIED WITH SECONDARY LOCK IN THE SAME BOX IN SAME Q.TY)


5) AGGANCIO SECONDARIO COMPLETAMENTE INSERITO, DOPO INSERIZIONE DI CONTATTI IN CAVITA'
(SECONDARY LOCK COMPLETELY MOUNTED, AFTER CONTACTS INSERTION INTO CAVITIES)

6) LE POLARIZZAZIONI -3 E -4 DIFFERISCONO DALLE -1 E -2 SOLAMENTE PER LA POSIZIONE DEL SISTEMA DI AGGANCIO A PANNELLO
(POLARIZATIONS -3 AND -4 ARE DIFFERENT FROM -1 AND -2 ONLY FOR THE PANEL HOOK DEVICE POSITION)

P/N 284879-1 COME MOSTRATO (CODICE A)
(P/N 284879-1 AS SHOWN (CODING A))

VEDI FOGLIO 2 PER LE ALTRE POLARIZZAZIONI
(SEE SHEET 2 FOR OTHER POLARIZATIONS)

1	ROSSO (RED)	PA66 GF30	DISPOSITIVO AGGANCIO SECONDARIO (SECONDARY LOCK)	2
1	NERO, GRIGIO, MARRONE (BLACK, GREY, BROWN)	PA66 GF20	BLOCCHETTO PORTACONTATTI (HOUSING)	1
Q.TA' (Q.TY)	COLORE (COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)	NO. (ITEM)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. POLIZZI 25JUL2002	 TE Connectivity	
DIMENSIONS: mm		CHK O. CANUTO 25JUL2002		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±1° FINISH -		AMP MCP 1.5/2.8 TAB HOUSING 20 POS. ASS'Y - UNSEALED	
MATERIAL SEE TABLE VEDI TABELLA	PRODUCT SPEC 108-20243		SIZE A2	
APPLICATION SPEC 411-20071		CAGE CODE -		DRAWING NO C-284879
WEIGHT -		RESTRICTED TO -		SCALE 2:1
Customer Drawing		SHEET 1		OF 4
		REV C		

1471-9 (3/13)

