




- | | | | | | | | | | |
|----------------------------|----------------|------------------|------------------|------------------|----|---|---|---------------|--|
| SUPERSEDED
BY 5749621-9 | 9.47
[.373] | 71.86
[2.829] | 66.60
[2.622] | 62.23
[2.450] | 49 |  |  | 100 | 1-749621-8 |
| SUPERSEDED
BY 5749621-5 | 7.44
[.293] | 40.11
[1.579] | 34.85
[1.372] | 30.48
[1.200] | 24 |  |  | 50 | 1-749621-7 |
| | 7.44
[.293] | 51.54
[2.029] | 46.28
[1.822] | 41.91
[1.650] | 33 |  |  | 68 | 1-749621-6 |
| OBSOLETE | 7.44
[.293] | 40.11
[1.579] | 34.85
[1.372] | 30.48
[1.200] | 24 |  |  | 50 |  1-749621-5 |
| OBSOLETE | 7.44
[.293] | 31.22
[1.229] | 25.96
[1.022] | 21.59
[.850] | 17 |  |  | 36 | 1-749621-1 |
| OBSOLETE | 9.47
[.373] | 84.56
[3.329] | 79.30
[3.122] | 74.93
[2.950] | 59 |  |  | 120 | 1-749621-0 |
| OBSOLETE | 9.47
[.373] | 71.89
[2.829] | 66.60
[2.622] | 62.23
[2.450] | 49 |  |  | 100 | 749621-9 |
| | 9.47
[.373] | 59.16
[2.329] | 53.90
[2.122] | 49.53
[1.950] | 39 |  |  | 80 | 749621-8 |
| | 7.44
[.293] | 51.54
[2.029] | 46.28
[1.822] | 41.91
[1.650] | 33 |  |  | 68 | 749621-7 |
| OBSOLETE | 7.44
[.293] | 46.46
[1.829] | 41.20
[1.622] | 36.83
[1.450] | 29 |  |  | 60 | 749621-6 |
| SUPERSEDED
BY 5749621-5 | 7.44
[.293] | 40.11
[1.579] | 34.85
[1.372] | 30.48
[1.200] | 24 |  |  | 50 | 749621-5 |
| OBSOLETE | 7.44
[.293] | 33.76
[1.329] | 28.50
[1.122] | 24.13
[.950] | 19 |  |  | 40 | 749621-4 |
| OBSOLETE | 7.44
[.293] | 26.14
[1.029] | 20.88
[.822] | 16.51
[.650] | 13 |  |  | 28 | 749621-3 |
| | 7.44
[.293] | 24.87
[.979] | 19.61
[.772] | 15.24
[.600] | 12 |  |  | 26 | 749621-2 |
| OBSOLETE | 7.44
[.293] | 21.06
[.829] | 15.80
[.622] | 11.43
[.450] | 9 |  |  | 20 | 749621-1 |
| | E | D | C | B | A | SHELL
FINISH | CONTACT
FINISH | NO OF
POSN | PART
NUMBER |

4805 (3/11)