




LOC	DIST	REVISONS				
P	LTR	DESCRIPTION			DATE	APVD
B1		REVISED PER ECO-11-005301			07MAR11	HMR

NOTES:

1. MATERIAL:
1.1 HOUSING: UL94V-0; COLOR: SEE TABLE.
 ▲: NY9T, THERMOPLASTIC, HIGH TEMP.
 ▲: PBT, THERMOPLASTIC.
- 1.2 CONTACTS: PHOSPHOR BRONZE
1.3 SHELL: SPCC
1.4 BOARDLOCK: BRASS
1.5 RIVET: BRASS
2. FINISH:
2.1 CONTACT:
 GOLD PLATING ON CONTACT AREA,
 100µ" MIN. MATTE TIN PLATING ON SOLDERTAIL,
 50µ" MIN. NICKEL UNDERPLATED OVERALL.
- 2.2 BOARDLOCK:
 100µ" MIN. TIN PLATING
 50µ" MIN. NICKEL UNDERPLATED OVERALL.
- 2.3 SHELL: 50µ" MIN. NICKEL PLATING OVERALL.
- 2.4 RIVET: NICKEL PLATING OVERALL.
3. RECOMMENDED PCB THICKNESS: 1.6mm
4. WAVE SOLDER CAPABLE TO 265°C
 PER TE CONNECTIVITY SPEC. 109-202, CONDITION B.



DETAIL Z
(W/SCREWLOCKS OPTION)

	▲	300U BLUE	3.20	TRAY	10µ"	RIVET, THREADED W/O SCREW	5-1734344-3
OBSOLETE		300U BLUE	3.70	TRAY	30µ"	RIVET, THREADED W/O SCREW	2-1734344-4
		300U BLUE	3.20	TRAY	30µ"	RIVET, THREADED W/O SCREW	2-1734344-3
OBSOLETE		661C BLUE	2.67	TRAY	30µ"	RIVET, THREADED W/O SCREW	2-1734344-2
		661C BLUE	2.67	TRAY	G/F	W/FEMALE SCREWLOCKS (DETAIL Z)	1-1734344-2
		300U BLUE	3.20	TRAY	G/F	W/FEMALE SCREWLOCKS (DETAIL Z)	1-1734344-1
	▲	BLACK	2.67	TUBE	15µ"	W/FEMALE SCREWLOCKS (DETAIL Z)	1734344-5
		300U BLUE	3.20	TUBE	10µ"	RIVET, THREADED W/O SCREW	1734344-4
OBSOLETE		300U BLUE	3.20	TRAY	10µ"	RIVET, THREADED W/O SCREW	1734344-3
		661C BLUE	2.67	TRAY	G/F	RIVET, THREADED W/O SCREW	1734344-2
		300U BLUE	3.20	TRAY	G/F	RIVET, THREADED W/O SCREW	1734344-1
	HSG RESIN	PANTONE COLOR	'L'	PACKAGING	GOLD PLATING	FASTENER OPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± .3
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± .3
4 PLC ± .3
ANGLES ± 3°

SEE NOTE

FINISH

SEE NOTE

DWN J. LEE 16JAN2006

CHK S. HOU 16JAN2006

APVD W.J. KE 16JAN2006

PRODUCT SPEC

108-57541

QUALIFICATION TEST REPORT

501-57623

WEIGHT 9.0g/PCS(W/ SCREW)
11.1g/PCS(W/O SCREW)

CUSTOMER DRAWING

TE Connectivity

RCPT ASM, SZ 1, 15 POSN,
RT ANG, FRONT METAL, SHELL
AMPLIMITE HD-22

SIZE A3 CAGE CODE 00779 DRAWING NO C-1734344

RESTRICTED TO

SCALE

SHEET 1 OF 3

REV B1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

©

COPYRIGHT

BY

LOC

DIST


DW

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1.	-	-	-

NOTES:


- MATERIAL:
 - 1.1 TRAY: PVC
 - 1.2 SHIPPING CARTON: CORRUGATED FIBERBOARD
- DIMENSION:
 - 2.1 TRAY: L=320, W=230, H=18.9
 - 2.2 SHIPPING CARTON: L=361, W=245, H=272
- QUANTITY:
 - 3.1 PRIMARY PACKING: 100 PCS/TRAY
 - 3.2 SECONDARY PACKING: 10 TRAY/CARTON(1000PCS)
- CARTON WEIGHT:
 - 4.1 W/O SCREWLOCK
NET WEIGHT: 8.24 Kg
GROSS WEIGHT: 9.24 Kg
 - 4.2 WITH SCREWLOCK
NET WEIGHT: 10.24 Kg
GROSS WEIGHT: 11.24 Kg



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

RCPT ASM, SZ 1, 15 POSN,
RT ANG, FRONT METAL, SHELL
AMPLIMITE HD-22

SIZE

CAGE CODE

DRAWING NO

A3

00779

C=1734344

RESTRICTED TO

-

SCALE



-

SHEET

2 OF 3

REV

B1



1. MATERIAL:
 - 1.1 TRAY: PVC
 - 1.2 SHIPPING CARTON: CORRUGATED FIBERBOARD
2. DIMENSION:
 - 2.1 TRAY: L=560, W=17.8, H=27.4
 - 2.2 SHIPPING CARTON: L=600, W=245, H=195
3. QUANTITY:
 - 3.1 PRIMARY PACKING: 17 PCS/TURE
 - 3.2 SECONDARY PACKING: 25 TUPE/BOX
 - 3.3 THIRD PACKING: 2 BOX/CARTON(850PCS)
4. CARTON WEIGHT:
 - 4.1 W/O SCREWLOCK
NET WEIGHT: 8.24 Kg
GROSS WEIGHT: 9.24 Kg
 - 4.2 WITH SCREWLOCK
NET WEIGHT: 10 Kg
GROSS WEIGHT: 11 Kg

FINISH

~~RESTRICTED TO~~

REV - 1