




3M™ FOUR-WALL HEADER, 2500 SERIES
.100" X .100" LOW PROFILE, SURFACE MOUNT, STRAIGHT AND RIGHT ANGLE THROUGH-HOLE



25XX-60XX
STRAIGHT VERSION



25XX-50XX
RIGHT ANGLE VERSION



25XX-6VOC
SURFACE MOUNT VERSION

- * LOW PROFILE, SPACE SAVING DESIGN.
- * CENTER SLOT POLARIZATION PREVENTS MIS-INSERTIONS AND REDUCES INSERTION TIME.
- * DUAL SLOT POLARIZATION MEANS BROADER COMPATIBILITY WITH COMPETITIVE POLARIZATION DESIGNS (NOT AVAILABLE ON 6, 8 OR 10 POSITIONS).
- * OPTIONAL RETAINER CLIP FOR LOCKING SOCKETS IN PLACE AND INCREASING CONNECTION RELIABILITY IN VIBRATION-PRONE ENVIRONMENTS.
- * HIGH TEMPERATURE INSULATOR SUITABLE FOR "NO LEAD" SOLDERING OPERATIONS.
- * THROUGH HOLE VERSION SUITABLE FOR REFLOW SOLDERING USING "PASTE IN HOLE" TECHNIQUES.
- * EXPOSED SOLDER TAILS (ON RIGHT ANGLE VERSION) PROVIDE EASE OF CLEANING AND REDUCED REPAIR COST.
- * STRAIGHT SURFACE MOUNT VERSION AVAILABLE.

2 PHYSICAL :

INSULATOR :
MATERIAL : GLASS FILLED POLYESTER (PCT)
FLAMMABILITY : UL94V-0
COLOR : BLACK
CONTACT :
MATERIAL : COPPER ALLOY
PLATING :
UNDER PLATING : 100µ" (2.54µm) NICKEL-OVERALL
WIPING AREA : AVG. GOLD (SEE ORDERING INFORMATION)
SOLDER TAILS : 200µ" (5.08µm) TIN LEAD OR MATTE TIN (SEE ORDERING INFORMATION)
MARKINGS : 3M LOGO, PART IDENTIFICATION NUMBER AND ORIENTATION TRIANGLE

2 ELECTRICAL :

CURRENT RATING : 5.00A, 1 CONTACT POWERED
3.00A, 6 CONTACTS POWERED
1.75A, ALL CONTACTS POWERED
RATING CONDITIONS : EIA-364-070 METHOD 2, 30°C MAXIMUM
TEMPERATURE RISE, 20% DERATED. REFERENCE APPROPRIATE
3M PRODUCT SPECIFICATION FOR DETAILED CURRENT DERATING
CURVES.
INSULATION RESISTANCE : >1 X 10⁹Ω AT 500 V_{DC}
WITHSTANDING VOLTAGE : 1,000V_{RMS} AT SEA LEVEL

2 ENVIRONMENTAL :

TEMPERATURE RATING : -55°C TO 105°C
PROCESS RATING : 260°C, PER J-STD-020C, SINGLE PASS
MOISTURE SENSITIVITY LEVEL : 1 (PER J-STD-020C)

NOTES

1. REGULATORY INFORMATION:
ROHS COMPLIANT. SEE THE
REGULATORY INFORMATION
APPENDIX (RIA) IN THE
"ROHS COMPLIANCE" SECTION
OF WWW.3MCONNECTORS.COM FOR
COMPLIANCE INFORMATION.
2. IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND THAT
CONTAINED IN THE PRODUCT
SPECIFICATION, THE PRODUCT
SPECIFICATION TAKES PRECEDENT.
3. NOTCHES A & C WILL ACCOMODATE
3M POLARIZING KEY: N3518.
4. CONTACT TAILS .0245 (.622) WIRE
WITH .0075 (.191) CORNER WIRE
AND .028 (.072) DIAGONAL.
5. SOLDER STANDOFFS FACILITATE
.01 (.3) CLEARANCE ABOVE
BOARD FOR REFLOW SOLDERING.

DIMENSIONS: INCHES [MM]
[MM] IS REF. ONLY

DIMENSIONS: INCHES [MM]				M 56068		AUG 11, 2014		JNC		RS					
IS REF. ONLY				REVISED AND REDRAWN											
DESIGN REFERENCE				NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
ACCESS CODES						CSTIGLIONE		DATE		AUG 11, 2014		MFG		DATE	
						CHKD		DATE		APPR		R. SCHERER		SEP 05, 2014	
DIVISION				DIVISION CODE		 3M Center St. Paul, MN 55144				© 2013 3M COPYRIGHT 2015 This document and the information it contains are 3M property and may not be reproduced or further disseminated without the express permission or use or disclosed other than for 3M authorized purposes. All rights reserved.					
Interconnect Solutions				EMSD											
DO NOT SCALE DRAWING				SCALE 4 1										TOLERANCES EXCEPT AS NOTED	
				INCHES		TITLE		HEADER, 4-WALL, LO-PRO, .100 X .100, SMT, STRAIGHT & RA							
THIRD ANGLE PROJECTION				.00 ± .01 .000 ± .005 .0000 ±											
INTERPRET PER ASME Y14.5 2009				MILLIMETERS											
MAX. SURFACE ROUGHNESS Rz 1.6				0 ± .3 .00 ± .13 .000 ±		CAGE NUMBER		SIZE		DRAWING NO.		REV.			
☒ UNFINISHED SURFACES ☐ MARKED ONLY				ANGLES		D		78-5100-0770-7				M			
						MODEL		3000 SERIES		DET.		1ST		YES ☒ NO ☐	
										SHT		1		OF 4	

3M™ FOUR-WALL HEADER, 2500 SERIES
.100" X .100" LOW PROFILE, SURFACE MOUNT, STRAIGHT AND RIGHT ANGLE THROUGH-HOLE







TABLE 1				
PIN QTY.	DIM. "A"	DIM. "B"	POLARIZING NOTCHES	PIN QTY.
06	.588 [14.94]	.508 [12.90]	B	06
08	.688 [17.48]	.608 [15.44]	B	08
10	.788 [20.02]	.708 [17.98]	BC	10
14	.988 [25.10]	.908 [23.06]	BCDE	14
16	1.088 [27.64]	1.008 [25.60]	ABCDE	16
20	1.288 [32.72]	1.208 [30.68]	ABCDE	20
24	1.488 [37.80]	1.408 [35.76]	ABCDE	24
26	1.588 [40.34]	1.508 [38.30]	ABCDE	26
30	1.788 [45.42]	1.708 [43.38]	ABCDE	30
34	1.988 [50.50]	1.908 [48.46]	ABCDE	34
36	2.088 [53.04]	2.008 [51.00]	ABCDE	36
40	2.288 [58.12]	2.208 [56.08]	ABCDE	40
50	2.788 [70.82]	2.708 [68.78]	ABCDE	50
60	3.288 [83.52]	3.208 [81.48]	ABCDE	60
64	3.488 [88.60]	3.408 [86.56]	ABCDE	64



ORDERING INFORMATION
STRAIGHT VERSION

X25XX-60XX-XX


N= HIGH TEMP BLACK (PCT)
(RB, UB OR UG PLATING REQ'D)
BLANK= (UB OR UG PLATING)
PIN QUANTITY:
(SEE TABLE 1)
SOLDER TAIL:
02 = FOR .062 [1.57] THICK BOARD
03 = FOR .094 TO .125 [2.39 TO 3.18]
THICK BOARD

PLATING:
RB = 30μ" [0.76μm] AVG. GOLD
200μ" [5.08μm] MATTE TIN (RIA, E1 & C1 APPLY)
UG = 15μ" [0.38μm] AVG. GOLD
200μ" [5.08μm] 60:40 TIN-LEAD SOLDER TAILS
(RIA E3 & C2 APPLY)
UB = 30μ" [0.76μm] AVG. GOLD
200μ" [5.08μm] 60:40 TIN LEAD SOLDER TAILS
(RIA E3 & C2 APPLY)


RECOMMENDED HOLE PATTERN
SHOWN FROM COMPONENT SIDE

DESIGN REFERENCE		NEXT ASSEMBLY		M	56068	AUG 11, 2014		JNC	RS
REV		ECO		REVISED AND REDRAWN		DATE		DRFT	CHKD
CUST CODES		CUST CODES		DATE		DATE		DATE	
DIVISION		DIVISION CODE		DATE		DATE		DATE	
Interconnect Solutions		EMSD		DATE		DATE		DATE	
DO NOT SCALE DRAWING		SCALE 4/1		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
MARKED ONLY		MARKED ONLY		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
CAGE NUMBER		CAGE NUMBER		DRAWING NO.		DRAWING NO.		REV.	
D		D		78-5100-0770-7		78-5100-0770-7		M	
MODEL		MODEL		3000 SERIES		3000 SERIES		REV.	
LISTS		LISTS		YES		YES		NO	
SHT		SHT		2		2		OF 5	

.100" X .100" LOW PROFILE, SURFACE MOUNT, STRAIGHT AND RIGHT ANGLE THROUGH-HOLE



PIN QTY.	DIM. "A"	DIM. "B"	POLARIZING NOTCHES	PIN QTY.
06	.588 [14.94]	.508 [12.90]	B	06
08	.688 [17.48]	.608 [15.44]	B	08
10	.788 [20.02]	.708 [17.98]	BC	10
14	.988 [25.10]	.908 [23.06]	BCDE	14
16	1.088 [27.64]	1.008 [25.60]	ABCDE	16
20	1.288 [32.72]	1.208 [30.68]	ABCDE	20
24	1.488 [37.80]	1.408 [35.76]	ABCDE	24
26	1.588 [40.34]	1.508 [38.30]	ABCDE	26
30	1.788 [45.42]	1.708 [43.38]	ABCDE	30
34	1.988 [50.50]	1.908 [48.46]	ABCDE	34
36	2.088 [53.04]	2.008 [51.00]	ABCDE	36
40	2.288 [58.12]	2.208 [56.08]	ABCDE	40
50	2.788 [70.82]	2.708 [68.78]	ABCDE	50
60	3.288 [83.52]	3.208 [81.48]	ABCDE	60
64	3.488 [88.60]	3.408 [86.56]	ABCDE	64



N= HIGH TEMP BLACK (PCT) _____
(RB, UB OR UG PLATING REQ'D)
BLANK= (UB OR UG PLATING)

SOLDER TAIL: _____
 02 = FOR .062 [1.57] THICK BOARD
 03 = FOR .094 TO .125 [2.39 TO 3.18]
 THICK BOARD

```

RB = 30μ" [ 0.76μm ] AVG. GOLD
    200μ" [ 5.08μm ] MATTE TIN (RIA. E1 & C1 APPLY)
UG = 15μ" [ 0.38μm ] AVG. GOLD
    200μ" [ 5.08μm ] 60:40 TIN-LEAD SOLDER TAILS
    (RIA E3 & C2 APPLY)
UB = 30μ" [ 0.76μm ] AVG. GOLD
    200μ" [ 5.08μm ] 60:40 TIN LEAD SOLDER TAILS
    (RIA E3 & C2 APPLY)

```

Imaged: M.3 2/10/2015 8:32 AM UTC-06:00

D

C

B


A

D

C

B

A



SECTION C - C

TABLE 1					
PIN QTY.	DIM. "A"	DIM. "B"	POLARIZING NOTCHES	TAPE AND REEL PKG CODE	PIN QTY.
06	.588 [14.94]	.508 [12.90]	B	WD (44 MM)	06
08	.688 [17.48]	.608 [15.44]	B	WD (44 MM)	08
10	.788 [20.02]	.708 [17.98]	BC	WD (44 MM)	10
14	.988 [25.10]	.908 [23.06]	BCDE	WD (44 MM)	14
16	1.088 [27.64]	1.008 [25.60]	ABCDE	WD (44 MM)	16
20	1.288 [32.72]	1.208 [30.68]	ABCDE	WE (56 MM)	20
24	1.488 [37.80]	1.408 [35.76]	ABCDE	WE (56 MM)	24
26	1.588 [40.34]	1.508 [38.30]	ABCDE	WE (56 MM)	26
30	1.788 [45.42]	1.708 [43.38]	ABCDE	WF (72 MM)	30
34	1.988 [50.50]	1.908 [48.46]	ABCDE	WF (72 MM)	34
36	2.088 [53.04]	2.008 [51.00]	ABCDE	WG (88 MM)	36
40	2.288 [58.12]	2.208 [56.08]	ABCDE	WG (88 MM)	40
50	2.788 [70.82]	2.708 [68.78]	ABCDE	WG (88 MM)	50
60	3.288 [83.52]	3.208 [81.48]	ABCDE	WH (120 MM)	60
64	3.488 [88.60]	3.408 [86.56]	ABCDE	WH (120 MM)	64

ORDERING INFORMATION
SURFACE MOUNT VERSION




N25XX-6VOC-XX-XX

N = HIGH TEMP BLACK (PCT)
(RB PLATING REQ'D)

PIN QUANTITY:
(SEE TABLE 1)

PACKAGING OPTIONS:
WX = TAPE & REEL PACKAGING (SEE TABLE 1)

PLATING:
RB = 30µ" [0.76µm] AVG. GOLD
200µ" [5.08µm] MATTE TIN (RIA, E1 & C1 APPLY)



RECOMMENDED PAD LAYOUT

DESIGN REFERENCE		NEXT ASSEMBLY		M 56068		AUG 11, 2014		JNC		RS	
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD			
CUST CODES		CUST CODES		DATE		DATE		DATE		DATE	
DIVISION		DIVISION CODE		DATE		DATE		DATE		DATE	
Interconnect Solutions		EMSD		AUG 11, 2014		AUG 11, 2014		SEP 05, 2014			
DO NOT SCALE DRAWING		SCALE 4/1		TOLERANCES EXCEPT AS NOTED		3M		© 3M COPYRIGHT 2015			
THIRD ANGLE PROJECTION		INCHES .00 ±.01 .000 ±.005 .0000 ±		MILLIMETERS 0 ±.3 .00 ±.13 .000 ±		3M Center St. Paul, MN 55144		This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
MAX SURFACE ROUGHNESS		SURFACES		CAGE NUMBER		SIZE		DRAWING NO.		REV.	
MARKED ONLY		ANGLES		D 78-5100-0770-7		M		MODEL		REV.	
				3000 SERIES		DET		YES		NO	
				SHT 4 OF 5							


PART CUSTOMIZATION

THIS SPEC SHEET DETAILS OUR STANDARD OFFERING.

3M HAS SEVERAL CAPABILITIES THAT CAN PROVIDE A PART TAILORED TO YOUR SPECIFIC NEEDS. ASK YOUR 3M SALES REPRESENTATIVE OR CUSTOMER SERVICE FOR MORE DETAILS.

- * SELECTIVE PIN REMOVAL (FOR BOARD ASSEMBLY POLARIZATION).
- * DIFFERENT PIN LENGTHS.


POLARIZING KEY



3M PART NO.	MATERIAL	COLOR	DIM. "A"
N3518	LCP	BLACK	.02

NOTE:
#2216 B/A SCOTCHWELD CAN BE USED TO ADHERE KEYS.


LOW PROFILE LATCH



PART NO.	MATERIAL	COLOR
3505-33B	NYLON	BLACK



NOTE:
LATCHES NOT COMPATIBLE WITH REFLOW SOLDERING.
ATTACH LATCHES AFTER SOLDERING.

POLARIZING POST



PART NO.	MATERIAL	COLOR
3201-3	PCT	BLACK

SHORT/LONG SOCKET RETAINER CLIP



PIN QTY.	DIM. "A"
06	N/A
08	N/A
10	.81 [20.6]
14	1.02 [25.9]
16	1.12 [28.4]
20	1.32 [33.5]
24	1.52 [38.7]
26	1.63 [41.4]
30	1.83 [46.4]
34	2.03 [51.6]
36	N/A
40	2.33 [59.2]
50	2.83 [71.9]
60	3.33 [84.6]
64	3.53 [89.7]

NOTE:
STAINLESS STEEL WITH GRAY POLYURETHANE COATING.

3505-8XXX
CLIP HEIGHT CODE — PIN COUNT (SEE TABLE)
0 = .31 [7.9] FOR SOCKETS WITHOUT STRAIN RELIEF
1 = .53 [13.5] FOR SOCKETS WITH STRAIN RELIEF

DESIGN REFERENCE		NEXT ASSEMBLY		M 56068		AUG 11, 2014		JNC		RS	
REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD			
CUST CODES		CUST CODES		CUST CODES		CUST CODES		CUST CODES		CUST CODES	
DIVISION		DIVISION		DIVISION		DIVISION		DIVISION		DIVISION	
Interconnect Solutions		EMSD		EMSD		EMSD		EMSD		EMSD	
DO NOT SCALE DRAWING		SCALE 4 1		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED		TOLERANCES EXCEPT AS NOTED	
THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION		THIRD ANGLE PROJECTION	
INTERPRET PER ASME Y14.5 - 2009		INTERPRET PER ASME Y14.5 - 2009		INTERPRET PER ASME Y14.5 - 2009		INTERPRET PER ASME Y14.5 - 2009		INTERPRET PER ASME Y14.5 - 2009		INTERPRET PER ASME Y14.5 - 2009	
MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS		MAX SURFACE ROUGHNESS	
MARKED ONLY		MARKED ONLY		MARKED ONLY		MARKED ONLY		MARKED ONLY		MARKED ONLY	
CAGE NUMBER		CAGE NUMBER		CAGE NUMBER		CAGE NUMBER		CAGE NUMBER		CAGE NUMBER	
D 78-5100-0770-7		D 78-5100-0770-7		D 78-5100-0770-7		D 78-5100-0770-7		D 78-5100-0770-7		D 78-5100-0770-7	
MODEL		MODEL		MODEL		MODEL		MODEL		MODEL	
3000 SERIES		3000 SERIES		3000 SERIES		3000 SERIES		3000 SERIES		3000 SERIES	
DET		DET		DET		DET		DET		DET	
YES		YES		YES		YES		YES		YES	
NO		NO		NO		NO		NO		NO	
SHT 5 OF 5		SHT 5 OF 5		SHT 5 OF 5		SHT 5 OF 5		SHT 5 OF 5		SHT 5 OF 5	