




D






C



B




A



RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR-BRONZE.
- △ CONTACT FINISH:(A)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.00381 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- △ PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



△ OBSOLETE	NO	130	65	131.88	330	1-5223007-1
	NO	118	59	119.88	300	1-5223007-0
	NO	106	53	107.88	270	1-5223007-9
	NO	94	47	95.88	240	1-5223007-8
	NO	82	41	83.88	210	1-5223007-7
OBSOLETE	NO	70	35	71.88	180	1-5223007-6
	NO	58	29	59.88	150	1-5223007-5
	NO	46	23	47.88	120	1-5223007-4
△ OBSOLETE	NO	34	17	35.88	90	1-5223007-3
	NO	22	11	23.88	60	1-5223007-2
	YES	10	5	11.88	30	1-5223007-1
POSITIONING PEGS		C	B	A	NO OF SIGNAL POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER 19NOV04	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm		CHK R.WERTZ 19NOV04	NAME R.WERTZ 19NOV04	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL △ △ △		WEIGHT -		A1 00779 ©=5223007
CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV A2		