








1

2

3


4

SECTION
A-A



NOTES:

- 1.MATERIAL:
 - A. HEADER HOUSING: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - B. TERMINAL : TINBRONZE
2. PACKAGING ACCORDING TO GS-14-626
3. MARKING ACCORDING TO DRAWING 59500.
4. FOR MORE DETAILS REFER THE DRAWING 52088 (2X4 SIGNAL SOFIX BOARD CONNECTOR)



PLATING IN CONTACT AREA	
DASH NUMBER	PERFORMANCE LEVEL
-1XXLF	TELCORDIA CD
-2XXLF	TELCORDIA CD

5-ROHS INFORMATION:


- This product meets European Union Directives and other country regulations as described in GS-22-008.
- The housing will withstand exposure to 260° peak temperature for 10 second in a convection, infra-red or vapor phase reflow oven.
- See Application notes/procedures if they are available.
- Packaging spec see GS-14-920.

tr	ecn no	dr	date
B	LS05-0020	JTA	05/01/27
C	D006-0389	KS	06/09/13
D	D007-0360	KS	07/09/04
E	D007-0389	KS	07/09/25
F	M09-0372	SH	09/11/24
G	N00-0319	AZH	10/08/31
H	ELXN-15760	HJ	13/09/06


www.fciconnect.com		surface		tolerance std		projection		Scale	
Dr		R WEBER		15/02/02		1SD 1302		m	
Eng		J.Taron		6/01/05		TOLERANCES UNLESS OTHERWISE SPECIFIED		A4	
Cmr		P.Legare		6/01/05		ANGULAR		DRAWING SCALE	
Appr		P.Legare		6/01/05		LINEAR		ECN	
Product family		6/01/05		Product family		0X		ELXN-15760	
size		0X		0X		0.0XX		0.01	
0.0XX		0.0XX		0.0XX		0.0XX		0.05	
Spec ref		Spec ref		Spec ref		Spec ref		Spec ref	
52089		52089		52089		52089		52089	
Rev.		Rev.		Rev.		Rev.		Rev.	
H		H		H		H		H	

Product nr.	Made from			
	Row	QTY	Column	
			1	2
			3	4
52089-101LF	B	8	D	D
52089-201LF	A		N	N
52089-102LF	B	8	D	S
52089-202LF	A		N	N
52089-103LF	B	8	S	S
52089-203LF	A		R	N
52089-111LF	B	8	D	D
52089-211LF	A		N	N
52089-112LF	B	8	D	S
52089-212LF	A		N	N
52089-113LF	B	8	S	S
52089-213LF	A		R	N


SEE NOTE 5



52089-X01LF
52089-X11LF




52089-X02LF
52089-X12LF



52089-X03LF
52089-X13LF

Item	Dim A
N	5,75
D	5,00
R	5,00
S	5,75



Material		Spec ref	
Mat code		tolerance	
Heatreat		ISD 406	
Plating/Finish		ISD 1302	
Dr	R WEBER	15/02/02	ISD 1101
Eng	J.Taron	6/01/05	Product family
Chr	Plegare	6/01/05	Model Name
Appr	Plegare	6/01/05	Model Revision
PIP HEADER 2x4		SDFIX	
Sofix shielded 1/D		ECN	
Pro/E file		REL Level	
catalog no		52089	
CUSTOMER COPY		sheet 2 of 2	