





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



Customer to tie 8+10 for 10V.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3	@20°C
D.C. RESISTANCE	4-5	@20°C
D.C. RESISTANCE	5-6	@20°C
D.C. RESISTANCE	7-10	@20°C
D.C. RESISTANCE	8-11	@20°C
INDUCTANCE	1-3	10kHz, 100mVAC, Ls
SATURATION CURRENT		20% rolloff from initial
LEAKAGE INDUCTANCE	1-3	tie(4+5+6, 8+10+11), 100kHz, 100mVAC, Ls
DIELECTRIC	1-11	tie(3+4, 7+8), 4500VAC, 1 second
DIELECTRIC	1-6	625VAC, 1 second
URNS RATIO		(2-1):(3-2)
URNS RATIO		(3-1):(7-10)
URNS RATIO		(3-1):(8-11)
URNS RATIO		(3-1):(6-5)
URNS RATIO		(3-1):(5-4)

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC61558-2-16:
- Reinforced insulation for a primary circuit at a working voltage of 400VDC.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel	Angles: $\pm 1^\circ$	TRANSFORMER	750811611
		PKG-0927	Fractions: $\pm 1/64$		
6B	7/13	www.we-online.com/midcom	Decimals: $\pm .005$ [.13]	eiSos p/n: 750811611	SPECIFICATION SHEET 1 OF 1
6A	6/13	SEE REVISION SHEET FOR REVISION LEVEL	Footprint: $\pm .005$ [.13]		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[750811611](#)