




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
AF	50				H	REV PER 0710-0427-95	27/SEP/95
					H1	REV PER ECO-09-020932	07SEP09




- 1. WIRE RANGE: 0.5 – 1.4 mm² [20 – 16 AWG].
- 2. INSULATION RANGE: 2.29 – 3.18 [.090 – .125] DIA.
- 3. DIMENSION IN BRACKETS ARE IN INCHES.
- 4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION A-A SECTION B-B



4 OBSOLETE



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MINI		-	505034-3
MINI		PRE TIN	505034-2
STANDARD		PRE TIN	505034-1
APPLICATOR TYPE		FINISH	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± - MATERIAL 0.41 [.016] BRASS FINISH SEE TABLE		DR 2-18-94 T. BECK	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME BUTTON CONTACT SIZE B CAGE CODE 00779 DRAWING NO C-505034 SCALE 5:1 SHEET 1 OF 1
		CHK 2-18-94 R. SWING	
		APPD 4-03-95 R. GRAY	
		APPD 4-03-95 R. GRAY	
		PRODUCT SPEC -	
		APPLICATION SPEC -	
		WEIGHT -	