

92 Combination DIN and Flange Mount Power Relay/DPST-NO and DPDT 30 Amp Rating (DC and AC)



General Specifications

(UL 508)

Contact Characteristics			Units	92S7	92S11
Number and type of Contacts				DPST-NO	DPDT-NO
Contact materials				Silver Alloy	Silver Alloy
Thermal (Carrying) Current			A	30	30
Maximum Switching Voltage			V	300V	300V
Switching Current @ Voltage		~	Resistive	30A @ 277V 50/60Hz	30A @ 277V 50/60Hz
		⎓	Resistive	20A @ 28V	20A @ 28V
			HP	3 @ 240V 50/60Hz	3 @ 240V 50/60Hz
			HP	1 @ 120V 50/60Hz	1 @ 120V 50/60Hz
			Pilot Duty	720 VA	720 VA
Minimum Switching Requirement		Minimum	mA	500 @ 12 VAC/VDC	500mA @ 12 VAC/VDC
Coil Characteristics					
Voltage Range		~	V	12....240	12....240
		⎓	V	6....110	6....110
Operating Range		% of Nominal	~	80% to 120%	80% to 120%
			⎓	75% to 120%	75% to 120%
Average consumption			~	VA	4
			⎓	W	1.7
Drop-out voltage threshold			~	10%	10%
			⎓	10%	10%
Performance Characteristics					
Electrical Life (UL 508)	Operations @ Rated Current		(Resistive)	100,000	100,000
Mechanical Life	Unpowered			5,000,000	5,000,000
Operating time (response time)			ms	15	15
Dielectric	Between coil and contact	~	V	4000	4000
	Between poles	~	V	2000	2000
	Between contacts	~	V	1500	1500
Environment					
Product certifications	Standard version			UL, CE, CSA	UL, CE, CSA
Ambient air temperature around the device	Storage		°C	-40...+85	-40...+85
	Operation		°C	-40...+55	-40...+55
Vibration resistance	Operational		g-n	3, 10-55Hz	3, 10-55Hz
Shock resistance			g-n	10	10
Weight			grams	86	86

Part Number Builder

92	S	7	D	22D	-12
Series	Cover	Configuration	Current Type	Mounting	Voltage
92	S = Sealed dust cover	7 = DPST-NO 11 = DPDT	A = AC D = DC	22D = DIN rail mount cover	Coil Voltage





Standard Part Numbers

BOLD-FACED PART NUMBERS ARE NORMALLY STOCKED

Nominal Input Voltage	Coil Resistance (OHMS)	DIN Part Number	Supersedes Part Number	Contact Configuration
24 VAC, 50/60 Hz	250 Ω	92S7A22D-24	W92S7A22-24	DPST-NO
120 VAC, 50/60 Hz	1600 Ω	92S7A22D-120	W92S7A22-120	DPST-NO
240 VAC, 50/60 Hz	6500 Ω	92S7A22D-240	W92S7A22-240	DPST-NO
24 VAC, 50/60 Hz	250 Ω	92S11A22D-24	W92S11A22-24	DPDT
120 VAC, 50/60 Hz	1600 Ω	92S11A22D-120	W92S11A22-120	DPDT
240 VAC, 50/60 Hz	6500 Ω	92S11A22D-240	W92S11A22-240	DPDT
12 VDC	86 Ω	92S7D22D-12	W92S7D22-12	DPST-NO
24 VDC	350 Ω	92S7D22D-24	W92S7D22-24	DPST-NO
110/125 VDC	7255 Ω	92S7D22D-110	W92S7D22-110	DPST-NO
12 VDC	86 Ω	92S11D22D-12	W92S11D22-12	DPDT
24 VDC	1600 Ω	92S11D22D-24	W92S11D22-24	DPDT
110/125 VDC	6500 Ω	92S11D22D-110	W92S11D22-110	DPDT

WIRING DIAGRAMS



ONLY NECESSARY TERMINALS
ARE PRESENT ON
SINGLE THROW STYLES

