



RUBY-D711VG2AR

Intel® Xeon™ and Core™ i7/i5/i3 Processors based ATX Board with ECC DDR3 SDRAM, Dual Display, Dual Gigabit Ethernet and USB Ports



Rear I/O

FEATURES

- Intel® Xeon™ and Core™ i3, i5 and i7 Processors
- Four long DIMMs support dual channel DDR3 ECC/non-ECC SDRAM up to 32GB
- Dual Display by VGA / DVI / HDMI
- RAID Support
- PCIE slots support
- Six COM ports support
- Intel® Active Management Technology 7.0

SYSTEM

Processor	CPU & Package: Intel® Xeon™ and Core™ i3/i5/i7 processor in LGA1155 socket
Chipset/Core Logic	Intel® C206 Chipset
System Memory	Up to 32GB DDR3 1333/1066 ECC/non-ECC SDRAM on Four 240-pin DIMM sockets with dual channel mode
BIOS	AMI uEFI BIOS
Storage Devices	- SATA 3Gb(4 ports) + 6Gb(2 ports) - Support RAID 0/1/5/10
Watchdog Timer	Programmable via software from 0.5 sec. to 254.5 min.
Expansion Interface	- One PCIe x 16 slot - One PCIe8 slot(x4 signal) - One PCIe4 slot(x1 signal) - Four PCI slots
Hardware Monitoring	System monitor(fan, temperature, voltage)
Power Requirement	TBA
Dimension	305(L) x 244(W) mm; 12"(L) x 9.6"(W)
Environment	Operation temperature: 0~60° C Storage temperature: -20~80° C Operation humidity: 5~90% non-condensing
MTBF	TBD

I/O

MIO	- Six Serial ports: One RS232 and one RS-232/422/485 selectable at rear IO, three RS232 and one RS232/422/485 selectable ports internal - 16 GPIO internal - LPC pin header
Ethernet Interface	- Dual Gigabyte Ethernet Controller (Intel® 82579LM & 82574L) - PCI Express x1 interface based Gigabit Ethernet - Dual RJ-45 connector with two LED indicators
Audio	HD Audio interface, Mic-in, Line-in, Line-out
USB	Twelve USB 2.0 ports (Four ports external, Eight ports internal)

ORDERING GUIDE

Standard	RUBY-D711VG2AR ATX IMB. LGA1155 CPU. C206 . ECC DDR3 / DVI / HDMI / Dual GbE / COM / Audio / USB
----------	---

DISPLAY

Graphic Controller	- Intel® HD Graphics 3000 integrated Graphics Engine - Onboard dual independent display by VGA/ DVI/ HDMI
--------------------	--



American Portwell

Fremont CA Tel: +1-510-403-3399

E-mail: info@portwell.com

http: www.portwell.com