

TARGETED FOR OBSOLESCENCE



- RoHS Compliant
- 18 - 40 & 33 - 75V Input Range
- Each Channel Independently Current Limited
- High Efficiency: 87% Typical
- Excellent Cross Regulation
- 1500V_{DC} Isolation Between Input and Output
- 500 V_{DC} Channel to Channel Isolation
- Fixed Frequency Operation
- Operation to 100°C Baseplate Temperature
- 50μs Transient Recovery, 0-90% Load Step
- Primary & Secondary Remote On/Off
- Adjustable Output Voltage
- External Synchronization
- VKP60MT Series UL/cUL approved to UL1950 and VDE approved to EN60950-1

ISO9001
CERTIFIED



For full details go to
www.murata-ps.com/rohs

The VKP60LTC and VKP60MTC Series are members of the VK high density DC/DC converter family. They are multiple output DC/DC converters offered in both a 18-40 and 33-75 input voltage range. Their versatile architecture featuring fully isolated channels enables the system designer to utilize the converter in either a single, dual or triple output scheme without excessive minimum load requirements or cross regulation degradation.

The VKP60xTC's architecture results in an economical and practical solution for use in distributed power schemes for today's demanding

telecommunication and electronic data processing applications requiring ground separation between noise sensitive digital logic and bipolar analog components. The VKP60xTC's proprietary control circuitry responds to 50-100% load steps in 35μSeconds to within 1% of nominal V_{out}. The peak deviation will not exceed 7% of V_{out} for pulsed load slew rates in excess of 75 Amps per microsecond. The VKP60xTC is ideal for electronic data processing applications utilizing modern disk drives and low voltage micro-processors that require dynamic load current response while maintaining tight output voltage tolerances.

PRODUCT SELECTION CHART

MODEL	INPUT VOLTAGE (V _{DC})	RATED V _{OUT} (V _{DC})			RATED MAXIMUM I _{OUT} (A)		
		V1 (±)	V2 (±)	V3 (±)	V1(±)	V2(±)	V3(±)
VKP60LT312C	24 (18-40)	3.3	12	12	18	2.5	2.5
VKP60LT315C	24 (18-40)	3.3	15	15	18	2.0	2.0
VKP60LT512C	24 (18-40)	5.1	12	12	12	2.5	2.5
VKP60LT515C	24 (18-40)	5.0	15	15	12	2.0	2.0
VKP60MT312C	48 (33-75)	3.3	12	12	18	2.5	2.5
VKP60MT315C	48 (33-75)	3.3	15	15	18	2.0	2.0
VKP60MT512C	48 (33-75)	5.1	12	12	12	2.5	2.5
VKP60MT515C	48 (33-75)	5.0	15	15	12	2.0	2.0

TARGETED FOR OBSOLESCENCE

TARGETED FOR OBSOLESCENCE

TARGETED FOR OBSOLESCENCE

TARGETED FOR OBSOLESCENCE

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

SPECIFICATIONS, ALL MODELS

Specifications are at $T_{CASE} = +40^{\circ}\text{C}$ nominal input voltage unless otherwise specified.

INPUT	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
	Voltage Range					
	VKP60LTXXC Series		16	24	40	V _{DC}
	VKP60MTXXC Series		33	48	75	V _{DC}
	Reflected Ripple Current	Peak - Peak			220	mA
	Input Ripple Current	DC to 1KHz	50	60		dB
	Maximum Input Current	Output Power = 60 W				
	VKP60LTXXC Series	V _{IN} = 16V			6	A
	VKP60MTXXC Series	V _{IN} = 30V			3	A
	No Load Power Dissipation	P _{OUT} = 0, V _{IN MIN} < V _{IN} < V _{IN MAX}			6	W
GENERAL	Inrush Charge					
	VKP60LTXXC Series				0.29	mC
	VKP60MTXXC Series				0.165	mC
	Quiescent Operating Current					
	Primary On/Off Disabled			7.5	10	mA
	Secondary On/Off Disabled			15	25	mA

GENERAL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
	ISOLATION					
	Input to Output	Peak Test	1500			V _{DC}
	Input to Baseplate		1500			V _{DC}
	Channel to Channel	Any Channel to Channel	500			V _{DC}
	Resistance, Input to Output		10			MΩ
	Capacitance, Input to Output			2000		pF
	Leakage Current			180		oA, rms
	GENERAL					
	Set-point Accuracy				1	%
GENERAL	Turn-on Time			3.5	5	mSec
	Remote On/Off Control Inputs					
	Primary	Open Collector/Drain				
	Sink Current Logic Low	V _{IN} = V _{IN MAX}		24	7	mA
	V _{low}			48	0.8	V
	V _{high}				Open Collector	
	Secondary	Open Collector/Drain				
	Sink Current Logic Low				100	μA
	V _{low}				0.4	V
	V _{high}				Open Collector	
GENERAL	External Synchronization Input					
	Frequency		440		520	KHz
	Pulse Width		150		320	nSec
	Source Impedance				47	Ω
	Input High Voltage		4		5	V
	Input Low Voltage		0		1	V
	Input Impedance			470		Ω
	Switching Frequency		470	480	490	KHz
	Weight				3 (85)	oz (g)

* See Application Notes available on the web at www.murata-ps.com

** X = Either L (24) or M (48)

SPECIFICATIONS, ALL MODELS

Specifications are at $T_{CASE} = +40^{\circ}\text{C}$ nominal input voltage unless otherwise specified.

GENERAL <i>continued</i>	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
	TEMPERATURE	Case temperature				
	Operation/Specification		-40		+100	$^{\circ}\text{C}$
	Storage		-50		+125	$^{\circ}\text{C}$
	Shutdown		+100		+115	$^{\circ}\text{C}$
	Thermal Impedance	Case to Ambient		8.2		$^{\circ}\text{C}/\text{W}$

PARAMETER	CONDITIONS	V1			V2			V3			UNITS
		Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	
VKP60xT312C** OUTPUT	Output Power	Total Combined O/P Power = 60 Watts Max.		30	60	15	30	15	30		W
	Set Point Voltage	$I_O = I_{O, \text{Nom}}$		3.3		12.2		12.2			V
	Output Current, I_{OUT}	0.5	9	18	0	1.25	2.5	0	1.25	2.5	A
	Output Ripple, p-p	DC to 20MHz*		100	200	150	250	150	250		mV
	Output Adjust Range	*		3.15	3.80	Dependent on V1					V
	Output Temperature Drift			.02	.05	.02	.05	.02	.05		$\%/^{\circ}\text{C}$
	Line Regulation	$V_{IN, \text{Min}} \leq V_{IN} \leq V_{IN, \text{Max}}$ $I_O = I_{O, \text{Nom}}$		0.05	1.0	1.0	2.0	1.0	2.0		%
	Load Regulation	Min Load to Rated Load		0.50	1.0	See Regulation Curves			See Regulation Curves		%
	Current Limit Inception	Other Outputs Min Load		23		5.0		5.0			A
	Short-Circuit Current			19	25	4.0	5.0	4.0	5.0		A
	Transient Response	50 to 100% Load Step									mV
	Peak Deviation			150	250						mV
	Settling Time	V_{OUT} 1% of $V_{OUT, \text{Nom}}$		35	50						μSec
	Overvoltage Limit			4.2	5.0						V
	Efficiency	$I_{OUT1} = 9\text{A}, (I_{OUT2} + I_{OUT3}) = 2.5\text{A}$ F.L. $V_{IN} = \text{Nominal}$		85	86						%

PARAMETER	CONDITIONS	V1			V2			V3			UNITS
		Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	
VKP60xT315** OUTPUT	Output Power	Total Combined O/P Power = 60 Watts Max.		30	60	15	30	15	30		W
	Set Point Voltage	$I_O = I_{O, \text{Nom}}$		3.3		15.85		15.85			V
	Output Current, I_{OUT}	0.5	9	18	0	1	2	0	1	2	A
	Output Ripple, p-p	DC to 20MHz*		100	200	125	250	125	250		mV
	Output Adjust Range	See Application Notes*		3.15	3.80	Dependent on V1					V
	Output Temperature Drift			.02	.05	.02	.05	.02	.05		$\%/^{\circ}\text{C}$
	Line Regulation	$V_{IN, \text{Min}} \leq V_{IN} \leq V_{IN, \text{Max}}$ $I_O = I_{O, \text{Nom}}$		0.05	1.0	1.0	2.0	1.0	2.0		%
	Load Regulation	Min Load to Rated Load		0.50	1.0	See Regulation Curves			See Regulation Curves		%
	Current Limit Inception	Other Outputs Min Load		23		4.0		4.0			A
	Short-Circuit Current			19	25	3.2	4.0	3.2	4.0		A
	Transient Response	50 to 100% Load Step									mV
	Peak Deviation			150	250						mV
	Settling Time	V_{OUT} 1% of $V_{OUT, \text{Nom}}$		35	50						μSec
	Overvoltage Limit			4.2	5.0						V
	Efficiency	$I_{OUT1} = 9\text{A}, (I_{OUT2} + I_{OUT3}) = 2\text{A}$ F.L. $V_{IN} = \text{Nominal}$		85	86						%

* See Application Notes available on the web at www.murata-ps.com

** X = Either L (24) or M (48)

SPECIFICATIONS, ALL MODELS

Specifications are at $T_{CASE} = +40^{\circ}\text{C}$ nominal input voltage unless otherwise specified.

PARAMETER	CONDITIONS	V1			V2			V3			UNITS
		Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	
Output Power	Total Combined O/P Power = 60 Watts Max		30	60		15	30		15	30	W
Set Point Voltage	$I_{O, Nom}$		5.1			12			12		V
Output Current, I_{OUT}		0.5	6.0	12	0	1.25	2.5	0	1.25	2.5	A
Output Ripple, p-p	DC to 20MHz*		125	200		150	250		150	250	mV
Output Adjust Range	*	4.75		5.50		Dependent on V1					V
Output Temperature Drift			.02	.05		.02	.05		.02	.05	%/°C
Line Regulation	$V_{IN, Min} \leq V_{IN} \leq V_{IN, Max}$ $I_O = I_{O, Nom}$		0.05	0.10		1.0	2.0		1.0	2.0	%
Load Regulation	Min Load to Rated Load		0.50	1.0	See Regulation Curves			See Regulation Curves			%
Current Limit Inception	Other Outputs Min Load		16			5.0			5.0		A
Short-Circuit Current			12.6	16		4.0	5.0		4.0	5.0	A
Transient Response	50 to 100% Load Step										
Peak Deviation			200	300							mV
Settling Time	V_{OUT} 1% of $V_{OUT, Nom}$		35	50							μSec
Overvoltage Limit		6.0		6.8							V
Efficiency	$I_{OUT1}=6A, (I_{OUT2}+I_{OUT3})=2.5A$ F.L. V_{IN} =Nomina	86	87								%

PARAMETER	CONDITIONS	V1			V2			V3			UNITS
		Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	
Output Power	Total Combined O/P Power = 60 Watts Max		30	60		15	30		15	30	W
Set Point Voltage	$I_{O, Nom}$		5.0			15.3			15.3		V
Output Current, I_{OUT}		0.5	6	12	0	1	2	0	1	2	A
Output Ripple, p-p	DC to 20MHz*		100	200		125	250		125	250	mV
Output Adjust Range	*		4.60		5.50			Dependent on V1			V
Output Temperature Drift			.02	.05		.02	.05		.02	.05	%/°C
Line Regulation	$V_{IN, Min} \leq V_{IN} \leq V_{IN, Max}$ $I_O = I_{O, Nom}$		0.05	0.10		1.0	2.0		1.0	2.0	%
Load Regulation	Min Load to Rated Load		0.50	1.0	See Regulation Curves			See Regulation Curves			%
Current Limit Inception	Other Outputs Min Load		16			4.0			4.0		A
Short-Circuit Current			12.6	16		3.2	4.0		3.2	4.0	A
Transient Response	50 to 100% Load Step										
Peak Deviation			200	300							mV
Settling Time	V_{OUT} 1% of $V_{OUT, Nom}$		35	50							μSec
Overvoltage Limit		6.0		6.8							V
Efficiency	$I_{OUT1}=6A, (I_{OUT2}+I_{OUT3})=2A$ F.L. V_{IN} =Nominal	86	87								%


* See Application Notes available on the web at www.murata-ps.com

** X = Either L (24) or M (48)

ORDERING INFORMATION	Device Family	VKp60	xTyz-	L	C
	Indicates 100 Watt Regulated Unit				
	Model Number	Selected from Table of Electrical Characteristics			
	Where:				
	x = Input Voltage (L = 24Voc, M = 48Voc)				
	T = Number of Outputs (Triple 'T')				
	y = 3 for 3.3V, 5 for 5V				
	z = 12 for 12V, 15 for 15V				
	Lead Length				
	0.250" - No Number				
0.145" - (6)					
0.110" - (8)					
RoHS Compliant					


TYPICAL PERFORMANCE CURVES

Specifications are at $T_{CASE} = +40^{\circ}\text{C}$ nominal input voltage, nominal load, recommended external components applied, unless otherwise specified.
(Refer to Application Note DCAN-9 at www.murata-ps.com)



EFFICIENCY vs TEMPERATURE

$T_{CASE} = +40^{\circ}\text{C}$, nominal input voltage, nominal load, recommended external components applied, unless otherwise specified.*




ABSOLUTE MAX. RATINGS


Output Short-Circuit Duration	Continuous
Baseplate Temperature	+100°C
Lead Temperature (soldering, 10 seconds max)	+300°C
Storage Temperature	+125°C
Input to Output Isolation	1500 V _{DC}

TYPICAL PERFORMANCE CURVES


VKP60xT312




VKP60xT315




VKP60xT512



VKP60xT515



MECHANICAL



NOTES:

All dimensions are in inches (millimeters).

PIN PLACEMENT TOLERANCE: $\pm 0.005"$

MECHANICAL TOLERANCE: $\pm 0.015"$

Marked with: specific model ordered, date code, job code.

MATERIAL: Units are encapsulated in a low thermal resistance molding compound which has excellent chemical resistance, wide operating temperature range, and good electrical properties under high humidity environments. The encapsulant and outer shell of the unit have UL94V-0 ratings. Lead material is matte tin 100 microinches min., over nickel, 40-80 microinches.

[A] See Ordering Information on page 4 for available lead lengths.

PIN CONNECTIONS

1	PRIMARY ON/OFF
2	-VIN
3	+VIN
4	SYNC IN
5	-V2
6	+V2
7	TRIM
8	+V1
9	-V1
10	SECONDARY ON/OFF
11	+V3
12	-V3