




DASH NO.	M CODE	MADE FROM
----------	--------	-----------



NOTES:

1. FOR USE WITH RG-174, 179, 187, 188 & 316/U CABLE.
2. FOR CABLING INSTRUCTIONS SEE CP-430.
3. FOR CRIMPING USE DIE KTH-2024.
4. INTERFACE PER MIL-STD-348, FIG. 301-2.
5. MATERIALS:
INSULATORS: TEFLON, ASTM-D-4894
K-GRIP SLEEVE: COM. BRONZE, ASTM-B-135
LOCKWASHER: PHOS. BRONZE, QQ-B-750
CENTER CONTACT: BER. COP., ASTM-B-196
ALL OTHER PARTS: BRASS, ASTM-B16-H02
6. FINISHES:
CENTER CONTACT: GOLD PLATE PER ASTM-B-488
ALL OTHER METAL PARTS: KINGS TARNISH RESISTANT FINISH (TR-5)
7. ELECTRICAL CHARACTERISTICS:
NOMINAL IMPEDANCE: 50 OHMS
VOLTAGE RATING: 500 VRMS
FREQUENCY RANGE: DC TO 4 GHz



MOUNTING HOLE

GSD

GSD

KC-19-152

REVISIONS		
ISSUE	CHANGES	
4	CN 33608 C REDRAWN JCA 12/18/91	
5	CN 34589 E JCA 04/19/93	
6	CN 35657 B KH 07/20/94	
7	CN 39182 D JPK 10/12/04	
8	CN 39807 C HVN 02/22/07	
KC-19-152 SD		
SCALE 4:1		
APPROX SURFACE AREA		
USED ON		
REF:		
JACK, BULKHEAD, BNC		
DRAWN	JCA	DATE 12/18/91
DESIGN	MJB	DATE 12/19/91
APPR.		DATE
 KINGS ELECTRONICS CO., INC. ROCK HILL, SOUTH CAROLINA 29730		
KC-19-152		