


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVO
AD	39		H2	REVISED PER ECO-11-004587	11MAR11	RK	HMR



- 1 ASSEMBLIES MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
- 3


.000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL ENTIRE POST
- 4

.000100-.000200 BRIGHT TIN OVER .000050 NICKEL ENTIRE POST
- 5

PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 6

HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR BLACK.
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

		5	4	1.584	1.500	15	16	4-103741-2
	OBSOLETE		4	1.384	1.300	13	14	4-103741-1
			3	3.984	3.900	39	40	4-103741-0
	OBSOLETE		3	3.884	3.800	38	39	3-103741-9
		7	3	3.784	3.700	37	38	3-103741-8
	SUPERSEDED BY 8-146282-7		3	3.684	3.600	36	37	3-103741-7
OBSOLETE		3	3.584	3.500	35	36	3-103741-6	
		3	3.484	3.400	34	35	3-103741-5	
		3	3.284	3.300	33	34	3-103741-4	
		3	3.284	3.200	32	33	3-103741-3	
		3	3.184	3.100	31	32	3-103741-2	
		3	3.084	3.000	30	31	3-103741-1	
		3	2.984	2.900	29	30	3-103741-0	
		3	2.884	2.800	28	29	2-103741-9	
		3	2.784	2.700	27	28	2-103741-8	
		3	2.684	2.600	26	27	2-103741-7	
		3	2.584	2.500	25	26	2-103741-6	
		3	2.484	2.400	24	25	2-103741-5	
		3	2.384	2.300	23	24	2-103741-4	
		3	2.284	2.200	22	23	2-103741-3	
		3	2.184	2.100	21	22	2-103741-2	
		3	2.084	2.000	20	21	2-103741-1	
		3	1.984	1.900	19	20	2-103741-0	
		3	1.884	1.800	18	19	1-103741-9	
		3	1.784	1.700	17	18	1-103741-8	
		3	1.684	1.600	16	17	1-103741-7	
3		1.584	1.500	15	16	1-103741-6		
3		1.484	1.400	14	15	1-103741-5		
3		1.384	1.300	13	14	1-103741-4		
3		1.284	1.200	12	13	1-103741-3		
3		1.184	1.100	11	12	1-103741-2		
3		1.084	1.000	10	11	1-103741-1		
3		.984	.900	9	10	1-103741-0		
3		.884	.800	8	9	103741-9		
3		.784	.700	7	8	103741-8		
3		.684	.600	6	7	103741-7		
3		.584	.500	5	6	103741-6		
3	.484	.400	4	5	103741-5			
3	.384	.300	3	4	103741-4			
3	.284	.200	2	3	103741-3			
3	.184	.100	1	2	103741-2			
3	.084	—	—	1	103741-1			
			PLATING	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. RINGLEY	7-19-85	 TE Connectivity						
DIMENSIONS: INCHES		CHK R. ELICKER	7-19-85							
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD R. ELICKER	NAME ASSEMBLY, MOD II, HEADER, BREAKAWAY, SINGLE ROW, .100 C/L, VERTICAL, WITH .025 SQ. POSTS						
	0 PLC ± -		PRODUCT SPEC							
	1 PLC ± -		—							
	2 PLC ± -		—							
	3 PLC ± -.005		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
	4 PLC ± -		—							
	ANGLES ± -		—							
	FINISH		—							
MATERIAL PHOSPHOR BRONZE		SEE TABLE	WEIGHT —	A2	00779	C=103741	—			
			CUSTOMER DRAWING		SCALE	4:1	SHEET	1 of 1	REV	H2