




Features:

- Available in three body types: Peel-A-Way® Removable Terminal Carriers, molded Solid Strips, and molded Snap Strips [breakable at .100/(2.54mm)].
- Tapered entry for ease of insertion.
- Multi-finger contacts for reliability.
- Closed bottom sleeve for 100% anti-wicking of solder.
- Custom configurations available.

Specifications:

Terminals:

Brass - Copper Alloy
(C36000) ASTM-B-16

Contacts:

Beryllium Copper
(C17200) ASTM-B-194

Solder Preform:

Standard: 63Sn/37Pb
Lead-free: 95.5Sn/4.0Ag/0.5Cu

Plating:

G - Gold over Nickel
M - Matte Tin over Nickel
T - Tin/Lead over Nickel

Gold per ASTM-B-488
Matte Tin per ASTM545-97
Tin/Lead per MIL-P-81728
Nickel per QQ-N-290




5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 Rev. August 08

Table of Models

	Description: Peel-A-Way® Strips (KSS) Material: Polyimide Film Index: -269°C to 400°C (-452°F to 752°F)	
	Description: Molded Snap Strips* (HSS, HLSS) Mat'l: Glass Filled Thermoplastic (PPS) Index: -60°C to 220°C (-76°F to 428°F)	
	Description: Molded Solid Strips (RNB, RLNB) Mat'l: High Temp. Liquid Crystal Polymer (LCP) Index: -40°C to 260°C (-40°F to 500°F)	

HSS/HLSS replaces RSS/RLSS and SS/LSS. RNB/RLNB replaces HNB/HLNB and NB/LNB.

Options




Tape Seal - add 3M to end of part number


- Removable tape seal protects plated contact in harsh environments.
- Sealed socket will not allow dirt and other contaminants to enter socket chamber and become entrapped behind contact fingers.
- Spray flux without contaminating contact area.
- Material - Silicone Backed Polyimide Film, -74°C to 260°C (-100°F to 500°F) Intermittent to 371°C (700°F)

Dimensional Information


Molded Body Types



Peel-A-Way® Body Types



How To Order



*PPS Insulators (HSS/HLSS) are not suitable for high temperature, lead-free (RoHS) solder profiles.

Note: Terminals plated with Matte Tin are available only with Gold plated contacts.

Quick-Turn delivery is not available on products with Matte Tin plating.

Products shown covered by patents issued and/or pending. Specifications subject to change without notice.

inch/(mm)


SIP Sockets Molded and Peel-A-Way® Insulators



Standard Quick-Turn Terminals

Additional standard and custom terminals available.
See Terminals section or consult factory.

Type -51	Type -04	Type -49	Type -01
		Not for use with HSS or RNB.	Molded only
Type -33	Type -85	Type -176	Type -210
Peel-A-Way® only	Peel-A-Way® only	Peel-A-Way® only	Peel-A-Way® only





Available Online:

- RoHS Qualification Test Report
- CAD Drawings

Solder Preform Terminals

Tin/Lead: Type -150 Lead-free: Type -811	Tin/Lead: Type -151 Lead-free: Type -812	Tin/Lead: Type -111 Lead-free: Type -810
		Peel-A-Way® only

Intrusive Reflow Application




Solder Preform Terminals

- Combines the labor of socket loading and solder application into one operation.
- Eliminates the use of solder paste and screening operation.
- Eliminates solder bridges and/or solder shorts due to excess solder.
- Ensures a reliable solder joint with controlled solder volume.
- Ideal for surface mount and mixed technology applications.
- For custom solder preform terminal applications consult factory.



5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 Rev. August 08



Features:

- Available in three body types: Peel-A-Way® Removable Terminal Carriers, molded Solid Strips, and molded Snap Strips [breakable at .100/(2.54mm)].
- Board to board applications.
- Peel-A-Way® Removable Terminal Carrier can be easily removed to allow inspection of solder joints on both sides of PC board, or left in place for added stability.
- Custom designs available.

Specifications:

Terminals:

Brass - Copper Alloy
(C36000) ASTM-B-16

Plating:

G - Gold over Nickel
M - Matte Tin over Nickel
T - Tin/Lead over Nickel

Gold per ASTM-B-488
Matte Tin per ASTM545-97
Tin/Lead per MIL-P-81728
Nickel per QQ-N-290


Table of Models

	Description: Peel-A-Way® Strips (KSA) Material: Polyimide Film Index: -269°C to 400°C (-452°F to 752°F)	
	Description: Molded Snap Strips* (HSA) Mat'l: Glass Filled Thermoplastic (PPS) Index: -60°C to 220°C (-76°F to 428°F)	
	Description: Molded Solid Strips (RNA) Mat'l: High Temp. Liquid Crystal Polymer (LCP) Index: -40°C to 260°C (-40°F to 500°F)	


HSA replaces RSA and SA, RNA replaces NA and HNA.

Dimensional Information


Molded Body Types



Peel-A-Way® Body Types



How To Order



*PPS Insulators (HSA) are not suitable for high temperature, lead-free (RoHS) solder profiles.
Note: Quick-Turn delivery is not available on products with Matte Tin plating.



5 Energy Way, West Warwick, RI 02893 USA
Tel: 800.424.9850 | 401.823.5200
Fax: 401.823.8723
info@advanced.com | www.advanced.com
Catalog 16 Rev. August 08

Products shown covered by patents issued and/or pending. Specifications subject to change without notice.

inch/(mm)


SIP Adapters Molded and Peel-A-Way® Insulators



Standard Quick-Turn Terminals

Additional standard and custom terminals available.
See Terminals section or consult factory.

Type -79 Peel-A-Way® only 	Type -80 Peel-A-Way® only 	Type -81 Peel-A-Way® only 	Type -574 Peel-A-Way® only (not Quick-Turn)
Type -08 Molded only 	Type -09 Molded only 	Type -68 Molded only 	Type -43 Molded only
Type -185 Molded only 	Type -42 Molded only 	Type -71 Molded only 	



Available Online:

- RoHS Qualification Test Report
- CAD Drawings