

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.								
LOC GP		DIST 00		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		A		NEW RELEASE		20NOV07	ZZQ	LZ

Receptacle

Printed Circuit Board

1.32±0.05

"A"±"T"

mating height:2.5 MAX

NOTES:
1. CABLE ASSEMBLY TO BE 100% TESTED FOR OPEN, SHORT & CONTINUITY
HI-POT:200 VDC FOR 100ms
INSULATION RESISTANCE: 50M OHMS MIN
CONTINUITY RESISTANCE: 2 OHMS MAX
FREQUENCY RANGE: DC TO 6 GHz
VSWR: 1.5:1 MAX

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ZhaoZhiqiang 20NOV07		Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:						NAME	
		0 PLC ± -		APVD JEFF ORNER 20NOV07		RF C/A, UMCC TO UMCC, TYPE III, 1.32MM CABLE			
		1 PLC ± -		PRODUCT SPEC		-			
		2 PLC ± -		APPLICATION SPEC		-			
		3 PLC ± -		-		-			
4 PLC ± -		ANGLES ± -		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		A300779		C-2015700	-
CUSTOMER DRAWING				SCALE		SHEET		REV	
				N.T.S.		1 OF 1		A	