





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED - NSD07-105	18JAN2008	GG	SJ
	B	REV PER ECO-14-004513	08APR2014	JB	MS

1 ALL DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.


2 POWER STRIP IS WIRED PER ELECTRICAL SCHEMATIC.

3 MATERIAL:
JUNCTION BOX HOUSINGS - POLYCARBONATE, UL 94V-0, BLACK.
JUNCTION BOX DUST COVER - 6/6, UL 94V-0 RATED.
JUNCTION BOX CONTACTS - COPPER ALLOY SELECTIVELY
TIN-PLATED AND SILVER PLATED 0.00508 [0.00200]
MINIMUM THICKNESS.
POWER STRIP BASE, COVER AND SCREW - ZINC PLATED CARBON STEEL.

4 APPLICATION:
AMPINERGY - MODULAR POWER DISTRIBUTION SYSTEM,
A MANUFACTURED WIRING SYSTEM.
THE POWER STRIP IS DESIGNED TO BE MOUNTED USING THE
KEYHOLE PATTERN IN THE MOUNTING BRACKET WITH
CUSTOMER SUPPLIED FASTENERS, 4 PLACES.



15/20 AMPINERGY DUPLEX RECEPTACLE
LINE 1, 2, 3, DEDICATED NEUTRAL
WITH STD. GND. () OR
ISOLATED GND. ()
4 REQUIRED




8 WIRE, DEDICATED NEUTRAL (3-3-2)
MULTIPLEX ASSEMBLY
2 PLACES

RECEPTACLE-QUANTITY/LINE/GROUND			PART NUMBER
	BLANK	9-1933415-9	
OBsolete	4 / (2) LINE 3 AND (2) LINE 3G	7-1933415-3	
OBsolete	4 / (2) LINE 2 AND (2) LINE 3G	7-1933415-2	
OBsolete	4 / (2) LINE 1 AND (2) LINE 3G	7-1933415-1	
OBsolete	4 / (2) LINE 3 AND (2) LINE 2G	6-1933415-3	
OBsolete	4 / (2) LINE 2 AND (2) LINE 2G	6-1933415-2	
OBsolete	4 / (2) LINE 1 AND (2) LINE 2G	6-1933415-1	
OBsolete	4 / (2) LINE 3 AND (2) LINE 1G	5-1933415-3	
OBsolete	4 / (2) LINE 2 AND (2) LINE 1G	5-1933415-2	
OBsolete	4 / (2) LINE 1 AND (2) LINE 1G	5-1933415-1	
OBsolete	4 / (2) LINE 2 AND (2) LINE 3	2-1933415-3	
OBsolete	4 / (2) LINE 1 AND (2) LINE 3	1-1933415-3	
OBsolete	4 / (2) LINE 1 AND (2) LINE 2	1-1933415-2	
OBsolete	4 / LINE 3G	1933415-7	
OBsolete	4 / LINE 2G	1933415-6	
OBsolete	4 / LINE 1G	1933415-5	
	4 / LINE 3	1933415-3	
	4 / LINE 2	1933415-2	
	4 / LINE 1	1933415-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 18JAN2008	 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK S. JONES 18JAN2008			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. JONES 18JAN2008	NAME	POWER STRIP, KEYHOLE MOUNT, 4 PORT, 3-3-2	
		PRODUCT SPEC	RESTRICTED TO -		
		APPLICATION SPEC			
		WEIGHT			
		CAGE CODE			
MATERIAL	FINISH	CUSTOMER DRAWING	SIZE	DRAWING NO	
- 3	- 3		A1	C=1933415	
			SCALE	SHEET	REV
			1:1	1 OF 3	B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
--		SEE SHEET 1	-	-	-



ELECTRICAL SCHEMATIC FOR
8-WIRE, DEDICATED NEUTRAL (3-3-2)
POWER STRIP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 18JAN2008	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK S. JONES 18JAN2008		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. JONES 18JAN2008	NAME POWER STRIP, KEYHOLE MOUNT, 4 PORT, 3-3-2	
	0 PLC ±"	PRODUCT SPEC	SIZE A 1	
	1 PLC ±"	APPLICATION SPEC	CAGE CODE -	
	2 PLC ±"	WEIGHT -	DRAWING NO. C=1933415	
MATERIAL -	ANGLES FINISH -	CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 3
			REV B	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
--		SEE SHEET 1	-	-	-

BLANK	BLANK/BLANK	BLANK/BLANK	BLANK	BLANK	BLANK/BLANK	BLANK/BLANK	BLANK	9-1933415-9
ISOLATED	N3/4	3G/8	15/20	STANDARD	N3/4	L3/8	15/20	7-1933415-3
ISOLATED	N3/4	3G/8	15/20	STANDARD	N2/3	L2/7	15/20	7-1933415-2
ISOLATED	N3/4	3G/8	15/20	STANDARD	N1/2	L1/6	15/20	7-1933415-1
ISOLATED	N2/3	2G/7	15/20	STANDARD	N3/4	L3/8	15/20	6-1933415-3
ISOLATED	N2/3	2G/7	15/20	STANDARD	N2/3	L2/7	15/20	6-1933415-2
ISOLATED	N2/3	2G/7	15/20	STANDARD	N1/2	L1/6	15/20	6-1933415-1
ISOLATED	N1/2	1G/6	15/20	STANDARD	N3/4	L3/8	15/20	5-1933415-3
ISOLATED	N1/2	1G/6	15/20	STANDARD	N2/3	L2/7	15/20	5-1933415-2
ISOLATED	N1/2	1G/6	15/20	STANDARD	N1/2	L1/6	15/20	5-1933415-1
STANDARD	N2/3	L2/7	15/20	STANDARD	N3/4	L3/8	15/20	2-1933415-3
STANDARD	N1/2	L1/6	15/20	STANDARD	N3/4	L3/8	15/20	1-1933415-3
STANDARD	N1/2	L1/6	15/20	STANDARD	N2/3	L2/7	15/20	1-1933415-2
ISOLATED	N3/4	3G/8	15/20	ISOLATED	N3/4	3G/8	15/20	1933415-7
ISOLATED	N2/3	2G/7	15/20	ISOLATED	N2/3	2G/7	15/20	1933415-6
ISOLATED	N1/2	1G/6	15/20	ISOLATED	N1/2	1G/6	15/20	1933415-5
STANDARD	N3/4	L3/8	15/20	STANDARD	N3/4	L3/8	15/20	1933415-3
STANDARD	N2/3	L2/7	15/20	STANDARD	N2/3	L2/7	15/20	1933415-2
STANDARD	N1/2	L1/6	15/20	STANDARD	N1/2	L1/6	15/20	1933415-1
GROUND TYPE	NEUTRAL NO./CONTACT NO.	LINE NO./CONTACT NO.	AMPERAGE	GROUND TYPE	NEUTRAL NO./CONTACT NO.	LINE NO./CONTACT NO.	AMPERAGE	PART NO.
LEFT-SIDE DUPLEX RECEPTACLE CONNECTIONS				RIGHT-SIDE DUPLEX RECEPTACLE CONNECTIONS				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
G. GARRETT
CHK
S. JONES
APVD
S. JONES

18JAN2008
18JAN2008
18JAN2008

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
±

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

SIZE
A1

CAGE CODE
-

DRAWING NO.
1933415

RESTRICTED TO
-

TE Connectivity

POWER STRIP, KEYHOLE MOUNT,
4 PORT, 3-3-2

SCALE
1:1

SHEET
3

OF
3

REV
B

4805 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[5-1933415-3](#)