







RECOMMENDED P.C.B. LAYOUT



CONTACT CONFIGURATION



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT MATERIAL: COPPER ALLOY W/ SILVER PLATE
5. RATING: 7A@125V, 4A@250
6. CONTACT RESISTANCE: 20MΩ MAX @ 5V DC 1A
7. DIELECTRIC STRENGTH: AC 1500V RMS
8. OPERATING FORCE: 550±150gf TYP.
9. TRAVEL: FULL:5.5, LOCK:4.0

|                                                                                                                    |         |                      |          |      |
|--------------------------------------------------------------------------------------------------------------------|---------|----------------------|----------|------|
| 9. TRAVEL: FULL:5.5, LOCK:4.0                                                                                      |         |                      |          |      |
| D                                                                                                                  | 15234   | UPDATED DESCRIPTION  | 9/2/05   | PH   |
| C                                                                                                                  | 11768   | REVISED DIMENSION    | 5/29/02  | CB   |
| B                                                                                                                  | 11768   | REVISED, AND REDRAWN | 10/23/01 | CJC  |
| REV.                                                                                                               | ECN No. | DESCRIPTION          | DATE     | CHKD |
| THE INFORMATION CONTAINED IN THIS DOCUMENT<br>IS PROPRIETARY TO E-SWITCH AND IS<br>NOT TO BE COPIED OR TRANSFERRED |         |                      |          |      |

|                  |          |              |         |     |
|------------------|----------|--------------|---------|-----|
| <b>E-SWITCH®</b> |          |              |         |     |
| TITLE            |          | P227 EE 1CXC |         |     |
| SCALE            | DATE     | DR           | DWG     | REV |
| 1.5:1            | 10/23/01 | CJC          | P030113 | D   |