






Technical drawing of a mechanical part with the following dimensions and features:

- Top horizontal dimension: 1.90 ± 0.05
- Left vertical dimension (from top surface): 1.98 ± 0.15
- Left vertical dimension (from bottom surface): 2.48 ± 0.15
- Bottom horizontal dimension (from left vertical line): 0.35 MIN
- Right vertical dimension (from bottom surface): 5.60
- Surface finish symbols:
 - Symbol 5 (triangle with 5) on the top horizontal surface.
 - Symbol 6 (triangle with 6) on the bottom horizontal surface.
- Internal features: A central cavity with a cross-section showing a central vertical slot and two curved internal surfaces.



SECTION E - E
SCALE 10:1



OBSOLETE	10	9	796068-
	7	2	796068
	RETENTION LEG FINISH	CONTACT FINISH	PART NUMBER

- | | | | | | |
|---|--|---|--|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN
CHG
01NOV97
1 SWANK
2 SWANK
10NOV97 | |  TE Connectivity | |
| DIMENSIONS:
mm | | TOLERANCES, UNLESS
OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ± | | NAME
RECEPTACLE ASSEMBLY, VERTICAL,
40 POSITION, PRESS FIT,
CHAMP BLINDMATE .050 SERIES 1 | |
| MATERIAL
 | | FINISH
SEE TABLE | | SIZE CASE CODE DRAWING NO
A100779C-796068 | |
| | | WEIGHT
- | | RESTRICTED TO | |
| | | CUSTOMER DRAWING | | SCALE 5:1 SHEET 1 OF 1 REV D | |