




PRODUCT SPECIFICATION

HDM3224-CWL

320 x240 COLOR GRAPHICS
LCD DISPLAY MODULE



HANTRONIX, INC. 10080 BUBB RD. CUPERTINO, CA 95014	Q.A.: ZW	REV.: 1.0	HDM3224-CWL	SHEET 1 OF 17
				DATE: 10/31/05

1.MECHANICAL DATA

NO	ITEM	CONTENTS	UNIT
1	Product No.	HDM3224-CWL	—
2	Module Size	154.6 (W) x 114.8 (H) x 9.0 (D)	mm
3	Dot Size	0.09 (W) x 0.33 (H)	mm
4	Dot Pitch	0.12 (W) x 0.36 (H)	mm
5	Number of Dots	320 x RGB (W) x 240 (H)	Dot
6	Duty	1/240	—
7	LCD Display Mode	FSTN, Color STN Module	—
8	Rear Polarizer	Color Transmission Type	—
9	Viewing Direction	6	O'clock
10	Backlight	LED	—
11	Controller	Excluded	—
12	DC/DC Converter	Excluded	—
13	Weight	195 (Approx.)	g

2. ABSOLUTE MAXIMUM RATINGS

(1) ELECTRICAL ABSOLUTE RATINGS

VSS=0V

ITEM	SYMBOL	MIN	MAX	UNIT	COMMENT
Power Supply for Logic	VDD-VSS	-0.3	6.5	V	
Power Supply for LCD Drive	VEE-VSS	0	30	V	
Input Voltage	VI	-0.3	VDD+0.3	V	
Static Electricity	-	-	-	-	Note 1

(2) ENVIRONMENTAL ABSOLUTE MAXIMUM RATINGS

ITEM	WIDE TEMP.			
	OPERATING		STORAGE	
	MIN.	MAX.	MIN.	MAX.
Ambient Temperature	−20	70	−30	80
Humidity (Without Condensation)	Note 2,4		Note 3,4	
Vibration	Note 5			

Note 1 LCM should be grounded during handling LCM.

Note 2 $T_a \leq 70^\circ\text{C}$: 75%RH max

$T_a > 70^\circ\text{C}$: Absolute humidity must be lower
than the humidity of 75%RH at 70°C

Note 3 T_a at -30°C will be < 48hrs, at 80°C will be < 120hrs

Note 4 Background color will change slightly depending on ambient temperature.
at phenomenon is reversible.

Note 5

Frequency	5 Hz~13.95 Hz	13.95 Hz~33 Hz	33 Hz~51 Hz	51 Hz~500 Hz
Vibration Level	-	$2 \times 9.8 \text{ m/s}^2$	-	$5 \times 9.8 \text{ m/s}^2$
Vibration Width	0.2 inch	-	0.036 inch	-
Vibration Direction	X/Y/Z			
Vibration Time	20 min/cycle X 3 directions			

HANTRONIX, INC. 10080 BUBB RD. CUPERTINO, CA 95014	Q.A.: Z.W.	REV.: 1.0	HDM3224-CWL	SHEET 3 OF 17
				DATE: 10/31/05

3. ELECTRICAL CHARACTERISTICS

3-1. ELECTRICAL CHARACTERISTICS OF LCM

Ta=25°C, VDD=3V/5V±5%

ITEM		SYMBOL	CONDITION		MIN.	TYP.	MAX.	UNIT
Logic Circuit Power Supply		VDD－VSS	Ta= 25℃		4.75	5.0	5.25	V
Logic Circuit Power Supply		VDD－VSS	Ta= 25℃		2.7	3.0	3.3	V
Input Voltage		VIH	H level		0.8VDD	－	VDD	V
		VIL	L level		0	－	0.2VDD	V
Recommended LCD Driving Voltage		VEE－VSS (Vop)	Duty=1/240 VDD=3V/5V	－20℃	27.0	27.4	27.8	V
				0℃	26.2	26.6	27.0	
				25℃	25.2	25.6	26.0	
				50℃	24.1	24.5	24.9	
				70℃	23.5	23.9	24.3	
Supply Current for Logic		IDD	VDD－VSS=3V/5V VEE－VSS=25.6V FLM=120Hz Ta=25℃ PATTERN : ■ □ ■ □ ■ □ ■ □ □ ■ □ ■ □ ■ □ ■		－	2.0	3.0	mA
Supply Current for LCD		IEE			－	4.8	7.2	mA
LCM	Surface Luminance	L	VEE－VSS =25.6V Ta=25℃ Vak=5V	PATTERN: (Dots All On of White Color)	70	－	－	cd/m ²
				PATTERN: (Dots All Off)	－	－	7	
Recommended Frame Frequency for Optimum Contrast		FLM	－		120	140	150	Hz

3-2.ELECTRICAL CHARACTERISTICS OF BACKLIGHT

Used LED Rating

Temp.=25°C

ITEM	SYMBOL	MIN.	TYP.	MAX.	UNIT	REMARK
Peak forward current	I_P	—	—	250	mA	—
Maximum reverse voltage	V_R	—	—	5	V	—
Applied forward current	I_F	—	—	200	mA	at $V_F = 5V$
Applied forward voltage	V_F	—	5	—	V	—
LED power consumption	P_F	—	—	1.25	W	—
LED life time	L_L	—	10000	—	hrs	at $I_F = 200\text{ mA}$ (*1)

(*1) LED life time is defined as follows : The final brightness is at 50% of original brightness .

4.OPTICAL CHARACTERISTICS

4-1.Optical Char. of Wide Temp. Mode

Cr>2 AT Vop

ITEM MODE	Cr(Contrast Ratio)										θ (Viewing Angle)		ϕ (Viewing Angle)	
	-20℃		0℃		25℃		50℃		70℃		25℃		25℃	
	MIN.	TYP.	MIN.	TYP.	MIN.	TYP.	MIN.	TYP.	MIN.	TYP.	MIN.	TYP.	MIN.	TYP.
T	12	18	14	20	17	25	3.5	5	1.4	2	—	F: >60 R: 30	—	L: 55 R: 55
NOTE		NOTE 6										NOTE 5		

note:

T: TRANSMISSIVE

M: For 6 O'clock Color STN Module

AT $\phi=0^\circ$ $\theta=0^\circ$

ITEM	SYMBOL	CONDITION	MIN.	TYP.	MAX.	UNIT	NOTE
Response Time (rise)	Tr	-20℃	2300	2900	4300	ms	NOTE 2
		0℃	640	800	1200		
		25℃	240	300	450		
		50℃	80	100	150		
		70℃	45	55	80		
Response Time (fall)	Tf	-20℃	1500	1800	2700	ms	NOTE 2
		0℃	360	450	670		
		25℃	80	100	150		
		50℃	48	60	90		
		70℃	32	40	60		

HANTRONIX, INC.
10080 BUBB RD.
CUPERTINO, CA 95014

Q.A.:
Z.W.

REV.:
1.0

HDM3224-CWL

SHEET 6 OF 17

DATE:
10/31/05

4-2.Color of CIE Coordinate


Ta = 25°C

ITEM		SYMBOL	CONDITION	VALUE	NOTE
Color of CIE Coordinate	Red	X	$\phi=0^\circ, \theta=0^\circ$	0.53	Note*
		y		0.33	
	Green	X	$\phi=0^\circ, \theta=0^\circ$	0.31	
		y		0.52	
	Blue	X	$\phi=0^\circ, \theta=0^\circ$	0.16	
		y		0.12	
	White	X	$\phi=0^\circ, \theta=0^\circ$	0.30	
		y		0.31	

Note* Measuring at position 3 on Fig.1
CIE chromaticity diagram

Tolerance : ± 0.05

Fig.1



HANTRONIX, INC.
10080 BUBB RD.
CUPERTINO, CA 95014

Q.A.:
Z.W.

REV.:
1.0


HDM3224-CWL

SHEET 7 OF 17


DATE: 10/31/05

(NOTE 1)

Definition of Operation Voltage(Vop)



(positive type)




(negative type)

***Conditions**


Viewing Angle : 0
Frame Frequency : 140Hz
Applying Waveform : 1/N duty 1/a bias

(NOTE 2)

Definition of Response Time(Tr,Tf)



(positive type)





(negative type)

***Conditions**

Operating Voltage : Vop
Viewing Angle (θ,φ) : (0,0)
Frame Frequency : 140Hz
Applying Waveform : 1/N duty 1/a bias


(NOTE 3)

Description of Measuring Equipment and Driving Waveforms





(NOTE 4)

Definition of Viewing Direction



(NOTE 5)

Definition of Viewing Angle




$$\theta = \theta_1 + \theta_2$$

***Conditions**


Operating Voltage : V_{op}
Frame Frequency : 140Hz
Applying Waveform : 1/N duty 1/a bias
Contrast Ratio : larger than 2

(NOTE 6)

Definition of Contrast Ratio (Cr)



(positive type)



(negative type)


$$\text{Contrast Ratio : } Cr = A/B$$

***Conditions**


Viewing Angle : 0
Frame Frequency : 140Hz
Applying Waveform : 1/N duty 1/a bias

5. BLOCK DIAGRAM

LCD



CCFL



6.INTERNAL PIN CONNECTION

LCD

Pin No.	Symbol	Function	Level
1	FRM	Synchronous signal for driving scanning line	H
2	LOAD	Data signal latch clock	H → L
3	CP	Data signal shift clock	H → L
4	DISP	Display control signal	H(ON),L(OFF)
5	VDD	Power supply for logic	—
6	VSS	GND	—
7	VEE	Power supply for LCD	—
8	D7	Display data	H(ON),L(OFF)
9	D6		
10	D5		
11	D4		
12	D3		
13	D2		
14	D1		
15	D0		

CN1 : 53261-1510(Molex)

Recommended Matching Connector : 51021-1500(Molex) or Compatible


LED

Pin No.	Symbol	Function	Level
1	A	Power supply for LED Backlight (+)	—
2	NC	NO Connection	—
3	K	Power supply for LED Backlight (-)	—

CN2 : BHR-03VS-1(JST)


Recommended Matching Connector : SM02-(8.0)B-BHS-1(JST) or Compatible

7. POWER SUPPLY



$$R1 + R2 + VR = 10 \sim 20K \Omega$$

$$C1, C2 = 10 \mu F$$




8.TIMING CHARACTERISTICS

8-1.INTERFACE TIMING

VDD=3.0/5.0V $\pm$ 10%

Parameter	SYMBOL	MIN.	MAX.	UNIT
CLOCK PULSE CYCLE TIME	t_{WCK}	66/40	—	ns
CLOCK PULSE HIGH LEVEL WIDTH	t_{WCKH}	23/12	—	ns
CLOCK PULSE LOW LEVEL WIDTH	t_{WCKL}	23/14	—	ns
LATCH PULSE HIGH LEVEL WIDTH	t_{WLPH}	30/15	—	ns
CP→LP RISE TIME	t_{LD}	10/5	—	ns
CP→LP FALL TIME	t_{SL}	30/25	—	ns
LP→CP RISE TIME	t_{LS}	30/25	—	ns
LP→CP FALL TIME	t_{LH}	30/25	—	ns
CLOCK PULSE RISE/FALL TIME	t_r, t_f	—	50	ns
DATA SETUP TIME	t_{DS}	10/5	—	ns
DATA HOLD TIME	t_{DH}	25/15	—	ns
$\overline{DISPOFF}$ LOW LEVEL WIDTH	t_{WDL}	1.2	—	μs
$\overline{DISPOFF}$ CANCELLATION TIME	t_{SD}	100	—	ns



HANTRONIX, INC.
10080 BUBB RD.
CUPERTINO, CA 95014

Q.A.:
Z.W.



REV.:
1.0

HDM3224-CWL


SHEET 13 OF 17

DATE:
10/31/05

8-2.TIMING CHART



8-3. POWER ON/OFF TIMING



The missing pixels may occur when the LCM is driven beyond above power interface timing sequence.

HANTRONIX, INC. 10080 BUBB RD. CUPERTINO, CA 95014	Q.A.: Z.W.	REV.: 1.0	HDM3224-CWL	SHEET 15 OF 17
				DATE: 10/31/05

8-4.DISPLAY PATTERN

START DATA

	Y1			Y2			Y3		
X1	R1	G1	B1	R2	G2	B2	R3	G3	B3
	D7	D6	D5	D4	D3	D2	D1	D0	D7
X2	R1	G1	B1	R2	G2	B2	R3	G3	B3
	D7	D6	D5	D4	D3	D2	D1	D0	D7

Y318			Y319			Y320		
R318	G318	B318	R319	G319	B319	R320	G320	B320
D0	D7	D6	D5	D4	D3	D2	D1	D0
R318	G318	B318	R319	G319	B319	R320	G320	B320
D0	D7	D6	D5	D4	D3	D2	D1	D0

X239	R1	G1	B1	R2	G2	B2	R3	G3	B3
	D7	D6	D5	D4	D3	D2	D1	D0	D7
X240	R1	G1	B1	R2	G2	B2	R3	G3	B3
	D7	D6	D5	D4	D3	D2	D1	D0	D7

R318	G318	B318	R319	G319	B319	R320	G320	B320
D0	D7	D6	U5	D4	D3	D2	D1	D0
R318	G318	B318	R319	G319	B319	R320	G320	B320
D0	D7	D6	U5	D4	D3	D2	D1	D0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hantronix:](#)

[HDM3224-CWL](#)