





LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			EI	REVISED PER ECO-11-004917	12MAR2011	RK	HMR



- ① PHYSICAL PROPERTIES (STANDARD)
HOUSING: POLYESTER, UL 94V-0 RATED, COLOR: GRAY.
TUBULAR CONTACT: COPPER ALLOY, ZINC PLATED.
SCREW: STEEL, ZINC PLATED CLEAR CHROMATE.
- ② PHYSICAL PROPERTIES (DURAMAX)
HOUSING: POLYESTER, UL 94V-0 RATED, COLOR: GRAY.
TUBULAR CONTACT: COPPER ALLOY, NICKEL PLATED.
SCREW: COPPER ALLOY, NICKEL PLATED.
3. MECHANICAL
PITCH: .375
MOUNTING: STANDARD CHANNEL AND CLAMP.
OPERATING TEMPERATURE: 150°C MAX.
TORQUE: RECOMMENDED TIGHTENING TORQUE IS 8 IN-LBS.
4. ELECTRICAL
MAXIMUM CURRENT: 50A
OPERATING VOLTAGE: 600 V
WIRE RANGE: 8-22 AWG.
- ⑤ SEE RESTRICTED CUSTOMER DRAWING 4-1437394-7.

-	4-1437394-7 
	1546148-2
	1546148-1
MATERIAL / FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 15JAN2002 CHK S. YODER 15JAN2002 APVD S. YODER 15JAN2002		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±.010 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, TERMINAL BLOCK, NEMA, DOVETAIL BASE, MEDIUM DUTY, TUBULAR SCREW	
MATERIAL		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	CAGE CODE 00779
SEE TABLE		SEE TABLE		DRAWING NO C-1546148	
		CUSTOMER DRAWING		SCALE 3.1	SHEET OF REV E