









spec ref		---		dr		S Paulandian		2013/02/26		projection		MM		size		A2		scale		1:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Jackie Chen		2015/01/08						ecn no		ELX-DG-19888-1					
ASME Y14.5M						chr		-		-													
						appr		Collins Lu		2015/01/08		product family		AirMax VSE									
surface 		linear		0.X		±.3				title		AIRMAX VS2 R.A. RECEPTACLE ASS'Y, 4 PAIR, 120 POS, 10 IMLA, 20MM						dwg no		10124460		rev	
				0.XX		±.10																	
				0.XXX		±.050																	
		angular		0°		±.050		www.fci.com		cat. no.		-		Product- Customer Drw		sheet 1 of 3							



RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6, 8, & 11

spec ref		---		dr		S Paulpandian		2013/02/26		projection		MM		size		A2		scale		1:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Jackie Chen		2015/01/08						ecn no		ELX-DG-19888-1		rel level		Released			
ASME Y14.5M				chr		-		-															
				appr		Collins Lu		2015/01/08														product family	
surface		✓		linear		0.X		±.3				title		AIRMAX VS2 R.A. RECEPTACLE ASS'Y, 4 PAIR, 120 POS, 10 IMLA, 20MM		dwg no		10124460		rev		B	
				0.XX		±.10																	
				0.XXX		±.050																	
				angular		0°		±°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 3					

