



| LOC | DIST | REVISIONS |     |                           |           |            |
|-----|------|-----------|-----|---------------------------|-----------|------------|
|     |      | P         | LTR | DESCRIPTION               | DATE      | DWN   APVD |
| AJ  | 16   | C1        |     | REVISED PER ECO-06-018704 | 06SEP2006 | MC   JH    |



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 BERYLLIUM COPPER PER QQ-C-530.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81  $\mu$ m [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81  $\mu$ m [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204, 0.76  $\mu$ m [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 2769.



RECOMMENDED PANEL CUTOUT

PCB CONFIGURATION

|                                        |                                                                                                                                 |                                                                          |                                                                                  |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| OBSOLETE                               | 2.03±0.13 [.080±.005]                                                                                                           | 2.29±0.13 [.090±.005]                                                    | 414907-3                                                                         |
|                                        | 2.03±0.13 [.080±.005]                                                                                                           | 2.79±0.25 [.110±.010]                                                    | 414907-2                                                                         |
|                                        | 3.48±0.25 [.137±.010]                                                                                                           | 4.11±0.43 [.162±.017]                                                    | 414907-1                                                                         |
| B                                      |                                                                                                                                 | A                                                                        | PART NUMBER                                                                      |
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                                                                                                                 | DWN J. LIPPERT 7-7-94<br>CHK M. TOMCHAK 7-7-94<br>APVD J. LIPPERT 7-7-94 | tyco<br>Electronics<br>Tyco Electronics Corporation<br>Harriaburg, PA 17105-3608 |
| DIMENSIONS:<br>INCHES                  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± 0.20 [.008]<br>4 PLC ± -<br>ANGLES ± - | NAME<br>PRODUCT SPEC<br>APPLICATION SPEC                                 | JACK, RIGHT ANGLE, 75 OHM,<br>LOW PROFILE, PCB, BNC<br>-                         |
| MATERIAL<br>SEE NOTES 1 - 5            | FINISH<br>SEE NOTES 6 - 8                                                                                                       | SIZE<br>CAGE CODE<br>DRAWING NO<br>WEIGHT                                | RESTRICTED TO                                                                    |
| CUSTOMER DRAWING                       |                                                                                                                                 | A1 00779 C=414907                                                        | SCALE 4:1 SHEET 1 OF 1 REV C1                                                    |