


DESCRIPTION: POWER - RIGHT ANGLE - MALE - MACHINED - IP67



SPECIFICATIONS:

ELECTRICAL:

INSULATOR RESISTANCE:	5 G OHMS Min.
DIELECTRIC WITHSTANDING:	1,000VAC r.m.s.
OPERATING TEMPERATURE:	-55° C ~ +155° C
CONTACT RESISTANCE:	1.0 Milliohms Max.
POWER PINS:	40 AMPS

MECHANICAL:

CONTACT INSERTION FORCE:	4.5 Kg Max.
CONTACT SEPARATOR FORCE:	0.3Kg Min.

MATERIALS:


CONTACTS:	COPPER ALLOY
INSULATOR:	PBT UL94V-0 RATED, BLK
SHELL:	STEEL
BOARD LOCK:	BRASS, NICKEL PLATED
CINCHNUT:	BRASS, NICKEL PLATED
BRACKET:	STEEL, NICKEL PLATED

FINISH:

SHELL:	NICKEL
CONTACTS:	FULL GLOLD FLASH

684S5W5103L461

46 = 4-40 INSERTS /
BOARD LOCKS



MEETS IP67 STANDARDS

(SEE PAGE 2 FOR SEALING DETAILS)



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:	P. JENKINS	DATE:	8-22-11
CHECKED:		DATE:	
SCALE:	1.5 = 1	SHEET	1 OF 3
DWG NO.	684S5W5103L461	REV	0



DETAIL A-A
SHOWN FOR REFERENCE ONLY

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: P.JENKINS		DATE: 8-22-11	
		CHECKED:		DATE:	
NorComp	SCALE: 1.5 = 1		SHEET 2		OF 3
	DWG NO. 684S5W5103L461		REV 0		

