


11.1 maxi




86093967113H65121E1

86093967113H65AGLF

Technical drawing of a connector pin assembly. The drawing shows a cross-section of the assembly with the following dimensions:

- Overall length: $4.8^{+0.2}_0$
- Signal pins: 4 pins on the right side.
- Pin diameter: $\varnothing 0.6^{-0.07}_0$
- Pin length: $2.7^{+0.2}_0$
- Pin spacing: $2.6^{+0.3}_0$

component side



SEE DRAWING C-8609-0000A

SPECIFICATION 121 = 4 grounding pins in position : A1-A32-C1-C32
or SPECIFICATION AG=

European Views

rev	ecn no	dr	date
A	-	-	2000/06/15
B	LS05-001	JTA	2005/03/02
C	LS06-0095	LG0	2006/06/26
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface		tolerance std		projection		mm		
			ISO 1302 		ISO 406 ISO 1101						
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	ROUILLARD	2000/06/15	ANGULAR	LINEAR	0.X	±0.1	size	A3	Scale		
Eng	TARON	2000/06/15			0.XX	±0.1			1.5		
Chr	LEGARE	2000/06/15			0.XX* ±2°	0.XXX			±0.1	ECN LS06-0095	
Appr	LEGARE	2000/06/15	Product family				DIN 8609		Spec ref -		
			title STANDARD MALE 3 ROW 96 CONTACTS				no dwg no C-8609-0813			Rev.	
										C	
catalog no			-				CUSTOMER			sheet	of