

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HBDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	03DEC2015	YS.H	CHL

PART A

PART B

TE

OJE-SH-112LMH

12V

UL

CCC

8A 250V ~

D/E

MADE IN CHINA

OEG C

SEE NOTE 5

LOT NO.

0.45

0.3

0.3

14.9±0.5

3.8±0.3

0.3

18.2±0.5



10.2±0.5

7.6±0.2


12.7±0.2

2.54±0.2

1.71



CONNECTION FIGURE

FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H.SASAKI

CHK Y.OIKAWA

APVD S.NAGAI

PRODUCT SPEC

SEE PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

OJE-SH-LMH CUSTOMER DRAWING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C= 1461403

SCALE 5:1 SHEET 1 OF 2 REV E

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

1461403-5	OJE-SH-124LMH	107-79010	24V	OJE-SH-124LMH	f
1461403-4	OJE-SH-112LMH	107-79010	12V	OJE-SH-112LMH	e
1461403-2	OJE-SH-109LMH	107-79010	9V	OJE-SH-109LMH	d
1461403-1	OJE-SH-106LMH	107-79010	6V	OJE-SH-106LMH	c
1461403-3	OJE-SH-105LMH	107-79010	5V	OJE-SH-105LMH	b
1461403-6	OJE-SH-103LMH	107-79010	3V	OJE-SH-103LMH	a
TE PART NO	TE TYPE NAME	PACKAGE SPEC	PART B	PART A	TYPE

RELAY TYPE

© B NOTES:
1.LOT NO. SYSTEM AS FOLLOWING:

0547

WEEK
YEAR

© 5.ADD LOT NO. SYSTEM AS FOLLOWING:

1 1 A
I II III

I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....

7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY,
SUCH AS: A,B.....Z

		UV RESIN	SEEL (VENT HOLE)	16
		EPOXY RESIN	SEEL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag ALLOY	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

© 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

© 3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.

© 4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.SASAKI	-
DIMENSIONS: mm		CHK	Y.OIKAWA	-
		APVD	S.NAGAI	-
		PRODUCT SPEC	SEE PRODUCT SPEC	
		APPLICATION SPEC	-	
		WEIGHT	-	
MATERIAL	FINISH	CUSTOMER DRAWING		
		TE Connectivity		
		OJE-SH-LMH CUSTOMER DRAWING		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C= 1461403	-	
SCALE		5:1	SHEET	2 OF 2
			REV	E