


P.C. MOUNTING

O.P. (MM)	P.T. (MM)
8.5 ±0.3	1.1 MAX.



O.P. = OPERATING POINT
P.T. = PRE-TRAVEL





CIRCUIT: SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- ▲3. RATING: 0.4VA @20VAC OR DC
- ▲4. OPERATING FORCE: 150± 40 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN: Q990001)
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC



TITLE MS085R100F150V1A

SCALE 2:1

DATE 8/20/2007

DR BF

DWG Q970085

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	17564	RELEASED FOR PRODUCTION	8/20/07	BF
REV	PCR NO	DESCRIPTION	DATE	BY