

Low Cost Linear Power Supplies

Features

- ◆ Low Output Ripple
- ◆ Single and Multiple Outputs
- ◆ Excellent Line & Load Regulation
- ◆ Worldwide Voltage Taps
- ◆ Industry standard footprint
- ◆ Operation up to 70°C Ambients

Key Market Segments & Applications

- ◆ Test & Measurement Burn-in & Test, Automated
Test, Instrumentation,
Measurement, Detection
- ◆ Low noise applications
- ◆ Light Industrial



Specifications

Model		
AC Input	-	100/120/220/230/240VAC, 47-63Hz (derate by 10% for 50Hz operation)
Efficiency	-	5V: 45%, 12/15V: 55%, 24V: 60%
Transient Response	-	50us for 50% load change
EMI	-	FCC Class B, VDE0871 Level B
Output Adjustment	-	±5% for all outputs (except outputs 2 & 3 on triple output models)
Remote Sense	-	On all single output models, HDC12 & HDC15, and output 1 of triple output models
Line Regulation	-	±0.05% for 10% line change
Load Regulation	-	±0.05% for 50% load change
Ripple and Noise	-	<3mV peak to peak
Overcurrent Protection	-	Foldback with automatic recovery (Contact factory before adjusting)
Overvoltage Protection	-	Standard on 5V outputs set at 6.2V ±0.4V OVP12 module sold separately for other outputs (see model selector)
Cooling	-	Convection or forced air
Operating Temp. Range	-	0 to +70°C, derate 3%/°C above 50°C
Storage Temperature	°C	-55 to +85°C
Temperature coefficient	-	±0.01% per °C
Humidity	-	5 - 95% RH (non condensing)
Leakage Current	uA	<50uA
Vibration	-	MIL-STD-810C, Method 514
Shock	-	MIL-STD-810C, Method 516
Safety Agency Approval	-	UL60950-1, EN60950-1, CE Mark
Size	-	Please see outline drawings
Warranty	-	Two years


Note: See Installation Manual for full details, test methods of parameters and application notes

OBSOLETE

2 Output Module Codes

	Model	Output	Output (V)	Max Current (A)	Power (W)	
Single Output	HSB5-3-OVP	V1	5	3.0	15.0	
	HSC5-6-OVP	V1	5	6.0	30.0	
	HSN5-9-OVP	V1	5	9.0	45.0	
	HSD5-12-OVP	V1	5	12.0	60.0	
	HSB12-1.7	V1	12	1.7	20.4	
	HSC12-3.4	V1	12	3.4	40.8	
	HSN12-5.1	V1	12	5.1	61.2	
	HSB15-1.5	V1	15	1.5	22.5	
	HSC15-3	V1	15	3.0	45.0	
	HSN15-4.5	V1	15	4.5	67.5	
	HSB24-1.2	V1	24	1.2	28.8	
	HSC24-2.4	V1	24	2.4	57.6	
	HSN24-3.6	V1	24	3.6	86.4	
	HSD24-4.8	V1	24	4.8	115.2	
	HSB28-1.0	V1	28	1.0	28.0	
	HSC28-2.0	V1	28	2.0	56.0	
	HSN28-3.0	V1	28	3.0	84.0	
HSD28-4.0	V1	28	4.0	112.0		
Dual Output	HDA12-15	V1	+12/15	1.0/0.8	24.0	
		V2	-12/15	1.0/0.8		
HDB12-15	V1	+12/15	1.8/1.5	40.0		
		V2	-12/15	1.8/1.5		
HDC12	V1	12*	3.4	80.0		
		V2	12*	3.4		
HDC15	V1	15*	3.0	80.0		
		V2	15*	3.0		
Triple Output	HTC1	V1	5*	3.0	40.0	
		V2	+12/15	1.0/0.8		
		V3	-12/15	1.0/0.8		
HTD1	V1	5*	6.0	70.0		
		V2	+12/15	1.7/1.5		
		V3	-12/15	1.7/1.5		
Accessories	OVP12 Adjustable 6.2-34V, 8A continuous, 12A peak					
* Isolated Outputs						

H Outline Drawing



DIMENSIONS:

MODEL	A	B	C	D	E	F	G
HSB A	4.881 (124.0)	3.976 (101.0)	1.614 (41.0)	.314 (8.0)	3.385 (86.0)	4.13 (105.0)	-
HSC B	4.881 (124.0)	5.629 (143.0)	2.480 (63.0)	.472 (12.0)	4.881 (124.0)	4.13 (105.0)	1.28 (32.5)
HSN C	4.881 (124.0)	7.007 (178.0)	2.755 (70.0)	.472 (12.0)	6.259 (159.0)	4.13 (105.0)	1.259 (32.0)
HSD I	4.881 (124.0)	8.818 (224.0)	2.755 (70.0)	.590 (15.0)	7.992 (203.0)	4.13 (105.0)	1.259 (32.0)
HDA H	4.015 (102.0)	6.496 (165.0)	1.653 (42.0)	.314 (8.0)	5.748 (146.0)	3.38 (86.0)	-
HDB D	4.881 (124.0)	7.007 (178.0)	2.755 (70.0)	.472 (12.0)	6.259 (159.0)	4.13 (105.0)	1.259 (32.0)
HDC I	4.881 (124.0)	8.818 (224.0)	2.755 (70.0)	.590 (15.0)	7.992 (203.0)	4.13 (105.0)	1.259 (32.0)
HTC F	4.015 (102.0)	10.236 (260.0)	2.519 (64.0)	.314 (8.0)	9.251 (235.0)	3.38 (86.0)	1.259 (32.0)
HTD G	4.881 (124.0)	11.023 (280.0)	2.755 (70.0)	.590 (15.0)	7.480 (190.0)	4.13 (105.0)	1.259 (32.0)

WEIGHT:

MODEL	LBS
HSB	1.98
HSC	3.96
HSN	5.94
HSD	7.48
HDA	1.98
HDB	3.96
HDC	7.48
HTC	5.06
HTD	7.92

NOTE:

1. DIMENSIONS ARE IN INCHES EXCEPT DIMENSIONS () ARE IN MM.
2. .188 (4.8) HOLES FOR CUSTOMER MTG.

For Additional Information, please visit
us.tdk-lambda.com/lp/products/h-series.htm

Other Industrial Products

HWS	15 to 1800W single output (switching)
NNS	15 to 90W high reliability (linear)
ZWS	5 to 150W single output, universal input (switching)
VSB & VSC	10 to 150W single output, 115VAC input (switching)

OBSOLETE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TDK-Lambda:

[HDA-12-15](#) [HDB-12-15](#) [HDC12](#) [HDC15](#) [HSB-12-1.7](#) [HSB-15-1.5](#) [HSB-24-1.2](#) [HSC-12-3.4](#) [HSC-24-2.4](#) [HSC-28-2.0](#) [HSC-5-6-OVP](#) [HSD-28-4.0](#) [HSD-5-12-OVP](#) [HSN-12-5.1](#) [HSN-15-4.5](#) [HSN-24-3.6](#) [HSN-28-3.0](#) [HTC1](#) [HSC-15-3](#) [HSN-5-9-OVP](#) [HTD1](#) [HSD-24-4.8](#) [HSB-28-1.0](#) [HSB-5-3-OVP](#)