

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	1 / 20

LIQUID CRYSTAL DISPLAY MODULE

MODEL: NMTB-S000255FYHSGY-10A

Customer's No.:

Acceptance

Microtips Technology Inc.
 12F. No.31 Lane 169, Kang Ning St., His-Chih,
 Taipei Hsien, Taiwan, R.O.C.
 FAX: 886-2-26958625

Approved and Checked by

Approved by	Checked by		Made by
<div>微端</div> <div>2006/5/16</div> <div>張秀美</div>	<div>微端</div> <div>2006/5/16</div> <div>蔡宜夢</div>	<div>微端</div> <div>2006/5/16</div> <div>連俊傑</div>	<div>微端</div> <div>2006/5/16</div> <div>陳雅靖</div>



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	2 / 20

Revise Records

Rev.	Date	Contents	Written	Approved
A	2006/5/16	Preliminary Spec	Sherry Chen	Debbie Chang

Special Notes

Note1.	With Touch Panel attached.
Note2.	The LCD module is RoHS compliant
Note3.	
Note4.	
Note5.	



Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	3 / 20

CONTENTS

1.	General Specifications	4
2.	Electrical Specifications	5
2.1	Absolute Maximum Ratings	5
2.2	DC Characteristics	5
2.3	AC Characteristics (Read/Write operation sequence - 68 Type MPU)	6
2.4	Lighting Specifications	7
2.5	Spec. for touch panel	8
3.	Optical Specifications	9
3.1	LCD Driving Voltage Recommended	9
3.2	Optical Characteristics	9
3.3	Definition of Viewing Angle and Optimum Viewing Area	9
3.4	Definition of Viewing Angle θ_f and θ_b	10
3.5	Definition of Contrast C	10
4.	I/O Terminal	11
4.1	Pin Assignment	11
4.2	Example of Power Supply	12
4.3	Block Diagram	12
5.	Reliability Test	13
5.1	Test Item	13
5.2	Judgment Standard	13
6.	Appearance Standards	14
6.1	Inspection Conditions	14
6.2	Definition of Applicable Zones	15
6.3	Standards	15
7.	Handling and Precautions	17
8.	Warranty	18
9.	Dimensional Outlines	19



Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	4 / 20

1. General Specifications

Operating Temperature	: Min. -20°C ~ Max. 70°C
Storage Temperature	: Min. -30°C ~ Max. 80°C
Dot Pixels	: 128 (W) x 128 (H) dots
Dot Size	: 0.40 (W) x 0.40 (H) mm
Dot Pitch	: 0.43 (W) x 0.43 (H) mm
Viewing Area	: 60.0 (W) x 58.4.0 (H) mm
Outline Dimensions	: 69.5 (W) x 138.2* (H) x 5.3** max. (D) mm
	* With LED B/L & T/P Tail
	** Without B/L holder and A,K pad
Weight	: N/A.
LCD Type	: STN/ Yellow-Green, Positive-Mode / Transflective
Viewing Direction	: 6:00
Data Transfer	: 8-bit parallel data transfer
Backlight	: LED (Yellow-Green) Edge-Type
LCD LSI	: NJU6679A
Drawings	: As attached drawings



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	5 / 20

2. Electrical Specifications

2.1 Absolute Maximum Ratings

$V_{SS} = 0V$

Parameter	Symbol	Conditions	Min.	Max.	Units
Supply Voltage (Logic)	$V_{DD} - V_{SS}$	—	- 0.3	5.0	V
Supply Voltage (LCD Drive)	$V_{DD} - V_{EE}$	—	$V_{DD} - 18.0$	$V_{DD} + 0.3$	V
Input Voltage	V_I	—	- 0.3	$V_{DD} + 0.3$	V

2.2 DC Characteristics

$T_a = 25^\circ C, V_{SS} = 0V$

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Supply Voltage (Logic)	$V_{DD} - V_{SS}$	—	2.4	—	3.6	V
Supply Voltage (LCD Drive)	$V_{DD} - V_{EE}$	Shown in 3.1				V
High Level Input Voltage	V_{IH}	$V_{DD} = 3.3V \pm 10\%$	$0.8 V_{DD}$	—	V_{DD}	V
Low Level Input Voltage	V_{IL}	$V_{DD} = 3.3V \pm 10\%$	V_{SS}	—	$0.2 V_{DD}$	V
High Level Output Voltage	V_{OH}	$I_{OH} = 0.50mA$	$0.8 V_{DD}$	—	V_{DD}	V
Low Level Output Voltage	V_{OL}	$I_{OL} = 0.50mA$	V_{SS}	—	$0.2 V_{DD}$	V
Supply Current	I_{DD}	$V_{DD} - V_{SS} = 3.3V$	—	0.05	5.0	μA
	I_{EE}	$V_{DD} - V_{EE} = 15.0V$	—	40.0	80.0	μA



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	6 / 20


2.3 AC Characteristics (Read/Write operation sequence - 68 Type MPU)

$$V_{DD} = 3.0V \pm 10\%$$

Parameter		Symbol	Min.	Typ.	Max.	Condition	Units
Address Hold Time		t_{AH6}	10	--	--	--	ns
Address Set Up Time		t_{AW6}	0	--	--	--	ns
System Cycle Time(W)		$t_{CYC6}(W)$	270	220	--	--	ns
System Cycle Time(R)		$t_{CYC6}(R)$	350	--	--	--	ns
Enable Pulse Width	Read "H"	t_{EWH}	200	--	--	--	ns
	Write "H"		50	--	--	--	ns
	Read "L"	t_{EWL}	220	160	--	--	ns
	Write "L"		150	--	--	--	ns
Data Set Up Time		t_{DS6}	35	--	--	--	ns
Data Hold Time		t_{DH6}	15	--	--	--	ns
Access Time		t_{ACC6}	--	--	200	CL=100pF	ns
Output Disable Time		t_{OH6}	0	--	50		ns
Rise Time, Fall Time		t_r, t_f	--	--	15	--	ns

All timing are based on 20% and 80% of All timing are based on 20% and 80% of V_{DD} voltage level.

t_{CYC6} shows the cycle of the E signal in active CS.



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	7 / 20

2.4 Lighting Specifications

2.4.1 Absolute Maximum Ratings

Ta = 25°C

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Forward Current	I _F	--.	--	--	56	mA
Reverse Voltage	V _R	--	--	--	5.0	V
LED Power Dissipation	P _D	--	--	--	252	mW

2.4.2 Operating Characteristics

Ta = 25°C


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Forward Voltage	V _F	I _F = 40 mA	--	4.2	--	V
Luminance of Backlight Surface*	L		13	18	--	cd/m ²
Spectrum radiation bandwidth	Δλ		--	30	--	nm
Peak emission wavelength	λ _P		569	573	5767	nm
Luminance Tolerance*	--		--	30	--	%

*Measured from the surface of backlight.

*Luminance Tolerance = (Max. - Min./Max.) x 100%

*The specification described above are based on the measurement of Backlight A,K.

2.4.3 Schematics Related



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	8 / 20

2.5 Spec. for touch panel

Item	Unit	Standard value			Note
		Min.	Typ.	Max.	
Linearity	%	-1.5	--	1.5	
Terminal resistance	Ω	250	--	550	(Film side)
	Ω	350	--	650	(Glass side)
Rate Voltage	V	--	5.0	5.5	
Insulation resistance	M Ω	20	--	--	DC25V
Chattering	ms	--	--	15	
Transparency	%	80	--	--	JIS K-7105
Operating force	g	--	--	80	Stylus pen (R0.8mm) or with finger (R8.0mm)
Surface hardness	H	--	2	--	150gf, 45deg.
Input Life	--	--	--	--	1,000,000 times (with R8, 60°)
Pen sliding durability	--	--	--	--	100,000 times (with R0.8, 60°)
Newton ring	No unusual interference finger must show when seen through the surface sheet.			Detail criterion for inspection refer attached inspection sheet.	

Note : Touch panel is with clear film.



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	9 / 20

3. Optical Specifications

3.1 LCD Driving Voltage Recommended

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
LCD Driving Voltage Note 1	$V_{DD}-V_O$	Ta = -20 °C	18.7	19.3	--	V
		Ta = 25 °C	16.2	16.7	17.2	V
		Ta = 70 °C	--	15.9	16.4	V

Note 1 : Voltage (Applied actual waveform to LCD Module) for the best contrast. The range of minimum and maximum shows tolerance of the operating voltage. The specified contrast ratio and response time are not guaranteed over the entire range.

3.2 Optical Characteristics

Ta=25 °C, 1/128 Duty, 1/12 Bias, $V_{DD} = 3.3V$ (Note 4), $\theta = 0^\circ$, $\phi = 270^\circ$

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Contrast Ratio Note 1	C	$\theta = 0^\circ$, $\phi = 0^\circ$	--	9.0	—	--
Viewing Angle. CR ≥ 2 (Shown in 3.3)	Front-Back	$\theta_f - \theta_b$, $\phi = 0^\circ$	+30	to	-25	deg.
	Left-Right	$\theta_l - \theta_r$, $\phi = 0^\circ$	+30	to	-30	deg.
Response Time	Rise Note 2	T_{ON}	--	—	140	280 msec
	Decay Note 3	T_{OFF}	--	—	140	280 msec

Note 1 : Contrast ratio is defined as follows.

$$CR = L_{OFF} / L_{ON}$$

L_{ON} : Luminance of the ON segments, L_{OFF} : Luminance of the OFF segments


Note 2 : The time that the luminance level reaches 90% of the saturation level from 0% when ON signal is applied.

Note 3 : The time that the luminance level reaches 10% of the saturation level from 100% when OFF signal is applied.

Note 4 : Definition of Driving Voltage V_D . Assuming that the typical driving waveforms shown below are applied to the LCD Panel at 1/A Duty - 1/B Bias (A : Duty Number, B : Bias Number). Driving voltage V_D is defined as follows: $V_D = (V_{th1} + V_{th2}) / 2$

V_{th1} : The voltage VO-P that should provide 50% of the saturation level in the luminance at the segment which the ON signal is applied to.

V_{th2} : The voltage VO-P that should provide 50% of the saturation level in the luminance at the segment which the OFF signal is applied to.




3.3 Definition of Viewing Angle and Optimum Viewing Area




Microtips Technology Inc.


Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	10 / 20



3.4 Definition of Viewing Angle θ_f and θ_b



3.5 Definition of Contrast C
 $C = \text{Brightness of selected dot (B1)} / \text{Brightness of unselected dot (B2)}$



Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	11 / 20

4. I/O Terminal

4.1 Pin Assignment

LCD

No.	Symbol	Level	Function
1	V1	—	LCD driving voltage supplying terminal
2	V2	—	LCD driving voltage supplying terminal
3	V3	—	LCD driving voltage supplying terminal
4	V4	--	LCD driving voltage supplying terminal
5	V5	--	LCD driving voltage supplying terminal
6	VSS	--	GND (VSS=0V)
7	D7	I/O	Data bit 7 in parallel operation
8	D6	I/O	Data bit 6 in parallel operation
9	D5	I/O	Data bit 5 in parallel operation
10	D4	I/O	Data bit 4 in parallel operation
11	D3	I/O	Data bit 3 in parallel operation
12	D2	I/O	Data bit 2 in parallel operation
13	D1	I/O	Data bit 1 in parallel operation
14	D0	I/O	Data bit 0 in parallel operation
15	E	I	When connect to the 68 type MPU, the enable signal is “H” active
16	R/W	I	When connect to the 68 type MPU, R/W=“H” active
17	A0	I/O	When A0=“H”, display data=“L”, instruction
18	/CS	I	Chip select terminal. (Data I/O available during /CS=“L”)
19	/RES	I	Reset terminal. When /RES goes to “L”, the initialization is performed
20	VDD	--	Power supply for logic (VDD=3.3V)

LED Backlighting

No.	Symbol	Level	Function
1.	LEDA (LED+)	--	Power Supply for LED Backlight Anode (+)
2.	LEDK (LED-)	--	LED Backlight Power Supply Cathode (-)Ground Potential

TOUCH PANEL

Pin No.	Symbol	Level	Function
1.	XR(X2)	--	Touch Panel Signal --
2.	YU(Y2)	--	Touch Panel Signal --
3.	XL(X1)	--	Touch Panel Signal --
4.	YL(Y1)	--	Touch Panel Signal --




Microtips Technology Inc.


Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	12 / 20

4.2 Example of Power Supply

External power is applied for this model : All of V1 to V5 and Vout supply from outside internal power supply
(Instruction) (T1,T2) = (H,H).



4.3 Block Diagram




Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	13 / 20

5. Reliability Test

5.1 Test Item

No change on display and in operation under the following test condition.

No.	Test Item	Description	Condition	Note
1.	High Temperature (Operation)	Durability test under long time high temperature with electrical stress (voltage, current)	70°C ± 2°C 96hrs	
2.	High Temperature (Storage)	Durability test under long time high temperature storage	80°C ± 2°C 96hrs	4
3.	Low Temperature (Operation)	Durability test under long time low temperature with electrical stress (voltage, current)	-20°C ± 2°C, 96hrs	3
4.	Low Temperature (Storage)	Durability test under long time low temperature storage	-30°C ± 2°C, 96hrs	3, 4
5.	Damp Proof Test	Durability test under long time high temperature and high humidity	40°C ± 2°C, 90% RH 96hrs	3, 4
6.	Vibration Test	Total fixed amplitude: 1.5mm Vibration frequency: 10~55Hz One cycle 60 seconds to 3 directions of X, Y, Z for each 15 minutes	--	5
7.	Drop Test	<p>To be measured after dropping from 60cm high on the concrete surface in packing state.</p>  <p><i>Dropping method corner dropping</i> A corner: once <i>Edge dropping</i> B, C, D edge: once <i>Face dropping</i> E, F, G face: once</p>		

Note 1: Unless otherwise specified, tests will be conducted under the following condition,

Temperature : 25°C ± 2°C

Humidity : 65% ± 5%

Note 2: Unless otherwise specified, tests will be not conducted under functioning state.

Note 3: No dew condensation to be observed.

Note 4: The function test shall be conducted after 4 hours storage at the normal temperature and humidity after removed from the test chamber.

Note 5: Vibration test will be conducted to the product itself without putting it in a container.

5.2 Judgment Standard



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	14 / 20

Failure Mode	Test Item							Judgment Standard
	1	2	3	4	5	6	7	
Orientation	*	*	*	*	*			No remarkable degradation of appearance under bias/ non-bias condition
Current Value (IAC)	*	*	*	*	*			No remarkable increase
Contrast	*		*	*	*			No remarkable poor contrast
Domain	*	*	*	*	*			Less than 20% of all dots have reverse tilt of more than on third of one dot area.
Bubble (Inside Cell)	*	*	*	*	*	*		As per "Appearance Standard" (Note. including one which disappear after 25°C 2H)
Polarizer	*				*	*		As per "Appearance Standard" no remarkable appearance change
Glass Damage							*	As per "Appearance Standard"

- Note. 1. * is strong linkage between Failure Mode and Test Item.
2. Number of Test Item should be referred to former page.
3. Judgment and Standard value should be fixed by other inspection standard and criteria samples.

6. Appearance Standards


6.1 Inspection Conditions




Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	15 / 20

The LCD shall be inspected under 40W white fluorescent light. The distance between the eyes and the sample shall be more than 30cm. All directions for inspecting the sample should be within 45° against perpendicular line.



6.2 Definition of Applicable Zones



- A Zone : Active display area
- B Zone : Area from outside of "A Zone" to validity viewing area
- C Zone : Rest parts
- A Zone + B Zone = Validity viewing area

6.3 Standards


No.	Parameter	Criteria
-----	-----------	----------



Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	16 / 20

1.	Black and White Spots, Foreign Substances	(1) Round Shape																												
		<table><tr><th rowspan="2">Dimension (mm) \ Zone</th><th colspan="3">Acceptable Number</th></tr><tr><th>A</th><th>B</th><th>C</th></tr><tr><td>D ≤ 0.2</td><td>*</td><td>*</td><td>*</td></tr><tr><td>0.2 < D ≤ 0.3</td><td>3</td><td>5</td><td>*</td></tr><tr><td>0.3 < D ≤ 0.4</td><td>2</td><td>3</td><td>*</td></tr><tr><td>0.4 < D ≤ 0.5</td><td>0</td><td>1</td><td>*</td></tr><tr><td>0.5 < D</td><td>0</td><td>0</td><td>*</td></tr></table>	Dimension (mm) \ Zone	Acceptable Number			A	B	C	D ≤ 0.2	*	*	*	0.2 < D ≤ 0.3	3	5	*	0.3 < D ≤ 0.4	2	3	*	0.4 < D ≤ 0.5	0	1	*	0.5 < D	0	0	*	
		Dimension (mm) \ Zone		Acceptable Number																										
			A	B	C																									
		D ≤ 0.2	*	*	*																									
		0.2 < D ≤ 0.3	3	5	*																									
		0.3 < D ≤ 0.4	2	3	*																									
		0.4 < D ≤ 0.5	0	1	*																									
		0.5 < D	0	0	*																									
		D = (Long + Short)/2 *: Disregard																												
(2) Line Shape																														
<table><tr><th colspan="2">X (mm) \ Y (mm) \ Zone</th><th colspan="3">Acceptable Number</th></tr><tr><th colspan="2"></th><th>A</th><th>B</th><th>C</th></tr><tr><td>--</td><td>0.03 ≥ W</td><td>*</td><td>*</td><td>*</td></tr><tr><td>2.0 ≥ L</td><td>0.05 ≥ W</td><td>3</td><td>3</td><td>*</td></tr><tr><td>1.0 ≥ L</td><td>0.1 ≥ W</td><td>3</td><td>3</td><td>*</td></tr><tr><td>--</td><td>0.1 < W</td><td colspan="3">In the same way (1)</td></tr></table>	X (mm) \ Y (mm) \ Zone		Acceptable Number					A	B	C	--	0.03 ≥ W	*	*	*	2.0 ≥ L	0.05 ≥ W	3	3	*	1.0 ≥ L	0.1 ≥ W	3	3	*	--	0.1 < W	In the same way (1)		
X (mm) \ Y (mm) \ Zone		Acceptable Number																												
		A	B	C																										
--	0.03 ≥ W	*	*	*																										
2.0 ≥ L	0.05 ≥ W	3	3	*																										
1.0 ≥ L	0.1 ≥ W	3	3	*																										
--	0.1 < W	In the same way (1)																												
X : Length Y: Width *: Disregard																														
Total defects shall not exceed 5.																														
2.	Air Bubbles (between glass & polarizer)																													
		<table><tr><th rowspan="2">Dimension (mm) \ Zone</th><th colspan="3">Acceptable Number</th></tr><tr><th>A</th><th>B</th><th>C</th></tr><tr><td>D ≤ 0.3</td><td>*</td><td>*</td><td>*</td></tr><tr><td>0.3 < D ≤ 0.4</td><td>3</td><td>*</td><td>*</td></tr><tr><td>0.4 < D ≤ 0.6</td><td>2</td><td>3</td><td>*</td></tr><tr><td>0.6 < D</td><td>0</td><td>0</td><td>*</td></tr></table>	Dimension (mm) \ Zone	Acceptable Number			A	B	C	D ≤ 0.3	*	*	*	0.3 < D ≤ 0.4	3	*	*	0.4 < D ≤ 0.6	2	3	*	0.6 < D	0	0	*					
		Dimension (mm) \ Zone		Acceptable Number																										
			A	B	C																									
		D ≤ 0.3	*	*	*																									
		0.3 < D ≤ 0.4	3	*	*																									
		0.4 < D ≤ 0.6	2	3	*																									
		0.6 < D	0	0	*																									
		*: Disregard																												
		Total defects shall not exceed 3.																												





To be continued.....

No.	Parameter	Criteria
		<p>(1) Dot Shape (with Dent)</p> <p>0.15 ≥ </p> <p>As per the sketch of left</p>



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	17 / 20

		<p>hand.</p> <p>(2) Dot Shape (with Projection)</p>  <p>Should not be connected to next dot.</p>  <p>(3) Pin Hole</p>  <p>$(X+Y)/2 \leq 0.2\text{mm}$ (Less than 0.1mm is no counted.)</p> <p>(4) Deformation</p>  <p>$(X+Y)/2 \leq 0.2\text{mm}$</p> <p>Total acceptable number: 1/dot, 5/cell (Defect number of (4): 1pc.)</p>
4.	Polarizer Scratches	Not to be conspicuous defects.
5.	Polarizer Dirts	If the stains are removed easily from LCDP surface, the module is not defective.
6.	Complex Foreign Substance Defects	Black spots, line shaped foreign substance or air bubbles between glass & polarizer should be 5pcs maximum in total.
7.	Distance between different Foreign Substance defects	$D \leq 0.2$: 20mm or more $0.2 < D$: 40mm or more

7. Handling and Precautions

The Following precautions will guide you in handling our product correctly.

1 Liquid crystal display devices

1.1 The liquid crystal display device panel used in the liquid crystal display module is made of



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	18 / 20

- plate glass. Avoid any strong mechanical shock. Should the glass break handle it with care.
 - 1.2 The polarizer adhering to the surface of the LCD is made of a soft material. Guard against scratching it.
- 2 Care of the liquid crystal display module against static electricity discharge.
 - 2.1 When working with the module, be sure to ground your body and any electrical equipment you may be using. We strongly recommend the use of anti static mats (made of rubber), to protect work tables against the hazards of electrical shock.
 - 2.2 Avoid the use of work clothing made of synthetic fibers. We recommend cotton clothing or other conductivity-treated fibers.
 - 2.3 Slowly and carefully remove the protective film from the LCD module, since this operation can generate static electricity.
- 3 When the LCD module alone must be stored for long periods of time:
 - 3.1 Protect the modules from high temperature and humidity.
 - 3.2 Keep the modules out of direct sunlight or direct exposure to ultra-violet rays.
 - 3.3 Protect the modules from excessive external forces.
- 4 Use the module with a power supply that is equipped with an over current protector circuit, since the module is not provided with this protective feature.
- 5 Do not ingest the LCD fluid itself should it leak out of a damaged LCD module. Should hands or clothing come in contact with LCD fluid, wash immediately with soap.
- 6 Conductivity is not guaranteed for models that use metal holders where solder connections between the metal holder and the PCB are not used. Please contact us to discuss appropriate ways to assure conductivity.

8. Warranty

This product has been manufactured to your company's specifications as a part for use in your company's general electronic products. It is guaranteed to perform according to delivery specifications. For any other use apart from general electronic equipment, we cannot take responsibility if the product is used in medical devices, nuclear power control equipment, aerospace equipment, fire and security systems, or any other applications in which there is a direct risk to human life and where extremely high levels of reliability are required. If the product is to be used



Microtips Technology Inc.

Messrs.					
Product Specification	Model:	NMTB-S000255FYHSGY-10A	Rev. No.	Issued Date.	Page.
			A	May 16. 06	19 / 20

in any of the above applications, we will need to enter into a separate product liability agreement.

- 1 We cannot accept responsibility for any defect, which may arise from additional manufacturing of the product (including disassembly and reassembly), after product delivery.
- 2 We cannot accept responsibility for any defect, which may arise after the application of strong external force to the product.
- 3 We cannot accept responsibility for any defect, which may arise due to the application of static electricity after the product has passed your company's acceptance inspection procedures.
- 4 We cannot accept responsibility for industrial property, which may arise through the use of your product, with exception to those issues relating directly to the structure or method of manufacturing of our product. Microtips-origin longer than one year from Microtips production.

9. Dimensional Outlines

- See the next page.....



Microtips Technology Inc.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microtips Technology:](#)

[NMTB-S000255FYHSGY](#)