



3.5 GHZ VERTICAL POLARIZATION HIGH-PERFORMANCE 120° SECTOR ANTENNA

The Laird Technologies J34216V00-120N 3.5 GHz wideband, vertically polarized 120° sector antenna, covers the frequency band from 3.4 to 3.8 GHz. Extremely low side lobes, null fill below the horizon and uniform energy distribution within the coverage area are achieved thanks to our highly skilled engineering staff and the utilization of our proprietary Artificial Intelligence RF Optimizing development tool. The antenna meets all aspects of ETSI EN 302.326-3 SS3. Laird Technologies' suite of high-performance sector antennas feature proprietary design elements, resulting in extremely high levels of system performance and ruggedness while maintaining very slim profiles with low wind and ice loading.





FEATURES

- Best-in-class f/b ratio
- Maximum null fill below the horizon
- Extraordinary low side lobe performance
- Rugged tilt mount hardware included
- Robust carrier class construction

MARKETS

- Wireless broadband service provider
- Large carrier class deployment
- Optimized for MIMO space time processing
- Outstanding levels of antenna-to-antenna co-located isolation
- WiMAX

PARAMETER	SPECIFICATIONS
Frequency range	3.4 - 3.8 GHz
Gain @ 3.5 GHz	17.5 dBi
Maximum VSWR	1.7:1
3 dB beamwidth - Elevation	3.5°
3 dB beamwidth - Azimuth	120°
Elevation null fill	Down to -25°
Azimuth side lobes	ETSI EN 302.326-3 SS3
Polarization	Vertical
Lightning protection	DC-grounded
Minimum front-to-back isolation	ETSI EN 302.326-3 SS3, 30 dB
Maximum input power	30 W average, 360 W peak
Input impedance	50 ohm
Minimum cross-polarization	ETSI EN 302.326-3 SS3
Mechanical size	52.2 in x 5.7 in x 3.3 in
Antenna weight	3.5 kg
Wind survival rating	Operational 100 mph / survival 136 mph
Antenna connection	Type N female
Radome	ASA gray
Mount style	Mast mount
Mounting hardware	Tilt mount kit 1.5 in to 4.5 in diameter
Temperature	-40°C to +70°C



Mounting Kit: JBXRK-01-TM5

global solutions: local support™

Americas: +1.847.839.6907
IAS-AmericasEastSales@lairdtech.com

Europe: +1.32.80.7866.12
IAS-EUSales@lairdtech.com

Asia: +1.65.6.243.8022
IAS-AsiaSales@lairdtech.com

www.lairdtech.com

ANT-DS-J34216V00-120N 0511

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2011 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.