





NOTES:

1. MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY - PHOSPHOR BRONZE, NICKEL PLATING
CONTACT - BRASS, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC-1 GHz
C. VSWR(RETURN LOSS): 1.5 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 750 VRMS, MIN.
3. CRIMPED FERRULE
HEX CRIMP SIZE .128"
CONTACT PIN TO SOLDER

MNB1112A1-NT30G-179U-75		REVISIONS			
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	9/16/06	46130	KL

RECOMMENDED
CABLE STRIPPING DIM'S

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

GLOBAL P/N

31-70339

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:

0.5 - 6mm	6 - 30mm	30 - 120mm	ANGLES
±0.1mm	±0.2mm	±0.3mm	±1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

PART NO.

DRAWN

KATE

ENGINEER

APPROVED

CAD FILE

F:\DWG\MNB\1112A1\179U-75\NT30GSZ

DATE

09-Jun-06

DATE

09-Jun-06

DATE

6/12/06

TITLE

MINI BNC R/A CRIMP PLUG
(FOR RG-179/U,187A/U)

ITEM NO. 311112AAA19NC7F

CODE ID

74868

DWG SIZE

B

DRAWING NO.

MNB1112A1-NT30G-179U-75

REV

A

Amphenol RF

Danbury, CT, USA

Tainan, Taiwan

Shenzhen, China

www.amphenolrf.com

SCALE: 3/1

SHEET 2 OF 2