

Features


1 or 2 pole, 20 A relay for direct 35 mm rail mounting

- 17.4 mm wide
- Test button
- Identification label
- AC coils and DC coils
- 35 mm rail (EN 50022) mount
- Cadmium free contact material

22.21





- Single phase switch 1 NO (SPST-NO)
- 35 mm rail mount



22.22



- Double phase switch 2 NO (DPST-NO)
- 35 mm rail mount



Contact specification

Contact configuration	1 NO (SPST-NO)	2 NO (DPST-NO)
Rated current/Maximum peak current A	20/30	20/30
Rated voltage/Maximum switching voltage V AC	250/400	250/400
Rated load AC1 VA	5,000	5,000
Rated load AC15 (230 V AC) VA	1,000	1,000
Single phase motor rating (230 V AC) kW	—	—
Breaking capacity DC1: 30/110/220 V A	20/0.3/0.12	20/0.3/0.12
Minimum switching load mW (V/mA)	1,000 (10/10)	1,000 (10/10)
Standard contact material	AgSnO ₂	AgSnO ₂

Coil specification

Nominal voltage (U _N)	V AC (50/60 Hz)	8 - 12 - 24 - 48 - 110 - 120 - 230 - 240
	V DC	12 - 24 - 48 - 110
Rated power AC/DC VA (50 Hz)/W		3/1.25
Operating range	AC (50 Hz)	(0.85...1.1)U _N
	DC	(0.9...1.1)U _N

Technical data

Mechanical life	cycles	500 · 10 ³
Electrical life at rated load in AC1	cycles	50 · 10 ³
Operate/release time	ms	15/8
Maximum impulse duration		continuous
Insulation between coil and contacts (1.2/50 μs)	kV	4
Ambient temperature range	°C	-40...+40
Protection category		IP 20

Approvals (according to type)




Features

1 or 2 pole, 20 A relay
for direct 35 mm rail mounting

- 17.4 mm wide
- Test button
- Identification label
- AC coils and DC coils
- 35 mm rail (EN 50022) mount
- Cadmium free contact material

22.23

22.24



- Double phase switch
1NO+1NC (SPST-NO+SPST-NC)
- 35 mm rail mount

- Double phase switch 2 NC
(DPST-NC)
- 35 mm rail mount

Contact specification

Contact configuration	1NO+1NC (SPST-NO+SPST-NC)	2 NC (DPST-NC)
Rated current/Maximum peak current	A 20/30	20/30
Rated voltage/Maximum switching voltage V AC	250/400	250/400
Rated load AC1	VA 5,000	5,000
Rated load AC15 (230 V AC)	VA 1,000	1,000
Single phase motor rating (230 V AC)	kW —	—
Breaking capacity DC1: 30/110/220 V	A 20/0.3/0.12	20/0.3/0.12
Minimum switching load	mW (V/mA) 1,000 (10/10)	1,000 (10/10)
Standard contact material	AgSnO ₂	AgSnO ₂


Coil specification

Nominal voltage (U _N)	V AC (50/60 Hz)	8 - 12 - 24 - 48 - 110 - 120 - 230 - 240
	V DC	12 - 24 - 48 - 110
Rated power AC/DC	VA (50 Hz)/W	3/1.25
Operating range	AC (50 Hz)	(0.85...1.1)U _N
	DC	(0.9...1.1)U _N

Technical data


Mechanical life	cycles	500 · 10 ³	500 · 10 ³
Electrical life at rated load in AC1	cycles	50 · 10 ³	50 · 10 ³
Operate/release time	ms	15/8	15/8
Maximum impulse duration		continuous	continuous
Insulation between coil and contacts (1.2/50 μs)	kV	4	4
Ambient temperature range	°C	-40...+40	-40...+40
Protection category		IP 20	IP 20

Approvals (according to type)



Ordering information

Example: 22 series 35 mm rail mount relay, 1 NO (SPST-NO) 20 A contact, coil rated 24 V DC, contact material AgSnO₂.



Technical data

Contact specifications					
Nominal rate lamps					
incandescent (230V)	W	1,000			
compensated fluorescent (230V)	W	360			
Insulation					
Dielectric strength					
between supply and contacts	V AC	3,500			
between open contacts	V AC	2,000			
between adjacent contacts	V AC	2,000			
Other data					
Bounce time: NO / NC	ms	5 / 10			
Power lost to the environment					
without contact current	W	1.2			
with rated current	W	3.2 (22.21, 22.23)	5.2 (22.22, 22.24)		
 Screw torque	Nm	0.8	0.8		
Max. wire size		Coil terminals		Contact terminals	
		solid cable	stranded cable	solid cable	stranded cable
	mm²	1x4 / 2x2.5	1x2.5 / 2x2.5	1x6 / 2x6	1x6 / 2x4
	AWG	1x12 / 2x14	1x14 / 2x14	1x10 / 2x10	1x10 / 2x12

If the coil is operated for a prolonged period of time, adequate ventilation of the relays must be provided - suggested gap of 9 mm between adjacent relays.

Coil specifications

DC version data

Nominal voltage	Coil code	Operating range		Resistance	Consumption
U _N		U _{min}	U _{max}	R	I at U _N
V		V	V	Ω	mA
12	9.012	10.8	13.2	115	104.3
24	9.024	21.6	26.4	460	52.2
48	9.048	43.2	52.8	1,850	25.9
110	9.110	99	121	9,700	11.3

AC version data

Nominal voltage	Coil code	Operating range		Resistance	Consumption
U _N		U _{min}	U _{max}	R	I at U _N
V		V	V	Ω	(50 Hz) mA
8	8.008	6.8	8.8	6.5	360
12	8.012	10.2	13.2	13.5	245
24	8.024	20.4	26.4	41	135
48	8.048	40.8	52.8	186	68
110	8.110	93.5	121	970	26
120	8.120	102	132	1,380	24
230	8.230	195.5	253	4,200	12.5
240	8.240	204	264	4,400	12

Accessories



Sheet of marker tags, plastic, 24 tags, 9x17 mm

020.24

