



G150XTN05.0

Color TFT-LCD Module

Features

- LED Backlight w/ Driver Embedded
- Luminance: 350 nits
- 50,000hrs LED Life
- ATM, POS Application
- Minimum 3 years Product Life Support
- ◆ Sample: Jun. 2012
- ◆ MP: Sep. 2012

Specification

(Preliminary)

Size (inch)	15"
Model	G150XTN05.0
Resolution (pixel)	1024x768
Active Area (mm)	304.128(H) x 228.096(V)
Pixel Pitch (mm)	0.297
Mode	Normally White
LCD Surface	Anti-glare
Number of Colors	16.2M
View Angle (U/D/R/L)	60/70/80/80
Brightness(nit)	350
Contrast Ratio	700:1
Response Time (ms)	8
LED Life (hrs.)	50K
Power Consumption (W)	TBD
Supply Voltage (V)	3.3
Storage Temp. (°C)	-30 ~ +85
Operation Temp. (°C)	-30 ~ +85
Outline Dimensions (mm)	326.5 x 253.5 x 12
Weight (g)	TBD
Interface	LVDS

