






NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Foil Material: .002 thick 1145 aluminum
3. Interface Material: .0005 thick phase-change thermal compound, both sides.
Maximum shipping & storage temperature – 40°C
Reflow temperature – 60°C
Maximum recommended service temperature – 200°C
4. Thermal impedance: .030 °C/W-in² (.194 °C/W-cm²) @ 20psi
5. Thermal washers shall be packaged in quantities of 10 with oversize separators between them.
6. Used with Power DIP packages (Apex designators: CR, CU, DC & DD).
7. Power Devices part no. AL-232-164-APX
8. Box part number is G760 (2 7/8" x 2" x 1/4") – Gary Plastics.
9. Supplier is to label each plastic box with the Apex part number.

TOLERANCES - UNLESS OTHERWISE SPECIFIED		TITLE: THERMAL WASHER, P-DIP				MODEL: TW05	
.XX = ±.05 [.002]		SUBJECT: MECHANICAL DRAWING				REV: H	
.XXX = ±.005 [.0002]		ENGINEER: D-M	DRAWN BY: P.ECK	DCA: 12437	SPL: 1 OF 1	DATE: 14NOV12	
ANG. = ±2°							

