

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0768505008

Status:

Active

Overview:

Impact Backplane Connector and Cable Assembly System

Description:

Impact 100 Ohm 4 Pair Right-Angle Orthogonal Daughtercard, Right Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-76060-999-001 (PDF)

Application Specification AS-76060-9999-001 (PDF)

Application Specification AS-76850-990-001 (PDF)

Packaging Specification PK-70873-610-001 (PDF)

Symbol Footprint Data SYM-76850-5008 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Backplane Connectors

76850

Daughtercard, Orthogonal, Orthogonal Direct, Orthogonal Midplane

Application Tooling Documents

TM-622018799

Component Type

PCB Receptacle

Electrical Model

Yes

Overview

Impact Backplane Connector and Cable Assembly System

Product Name

Impact

UPC

884982297777

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to PCB

Stackable

96

96

Black

200

No

94V-0

Yes

None

High Performance Alloy (HPA)

Gold

Tin

High Temperature Thermoplastic

13.164/g

8

4

12

Right Angle

1.20mm

No

None

1.00mm

Tray


1.90mm, 2.15mm

1.90mm, 2.15mm

0.762µm

Yes

No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76850 Series

Mates With

76845 Impact 100 Ohm Backplane Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Press-In Tool for Daughter Card Module	622018677
Impact Daughter Card Extraction Tool	622024300

Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-76060-9999-001, AS-76850-990-001
Electrical Model Document	EE-76850-049, EE-76850-055
Packaging Specification	PK-70873-610-001
Product Specification	PS-76060-999-001
S-Parameter Model	SP-76850-049
Sales Drawing	SD-76850-004-001
Symbol/Footprint Data	SYM-76850-5008

This document was generated on 07/29/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION