

Coaxial Cable Connector 11_1023-C50-2-3/111_N

Description

Straight cable plug

Interface standards
DIN 41626/2



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Centre contact crimped
Outer 2contact crimped
Weight 0.0024 kg

Environmental Data

Operating temperature -55 °C to 125 °C
2011/65/EU (RoHS) compliant

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body | Brass | Gold Plating (Nickel underplated) |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | |

Related Documents

Outline drawing DOU-00006692
Catalogue drawing DOU-00006694
Assembly instruction DOC-0000179140

Ordering Information

Single package 11_1023-C50-2-3/111_NE
Bulk 100 pcs package 11_1023-C50-2-3/111_NH

Additional Information

Suitable cables RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG 174 /U