

Customer Information Sheet

DRAWING No.: SI621-XXR

SHEET 2 OF 2



IF IN DOUBT - ASK

(C)


NOT TO SCALE

THIRD ANGLE PROJECTION



ALL DIMENSIONS IN mm



SECTION X-X




REEL DETAILS




REELING DIRECTION

- NOTES:
1. QUANTITY PER REEL = 5,000.
 2. THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION).
 3. FOR LOOSE COMPONENTS, SEE SI621-XX..





COMPONENT SPECIFICATION:
MATERIAL = BRASS CW508L 1/2 HARD
FINISH
06 = 4µ 90/10 TIN/LEAD
46 = 4µ 100% TIN
ELECTRICAL:
CURRENT RATING = 10A (30°C TEMP RISE)
CONTACT RESISTANCE = 20mΩ MAX
ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +125°C

ORDER CODE:
SI621-XXR
FINISH
06 = 4µ 90/10 TIN/LEAD OVER NICKEL
46 = 3µ 100% TIN OVER NICKEL



COMPONENT DETAILS



RECOMMENDED PAD LAYOUT

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

S/AREA:

mm²

TITLE:

SURFACE MOUNT JUMPER
(TAPE AND REELED)

DRAWING NUMBER:

SI621-XXR

SHT

2 OF 2

MSP	9	16.10.15	13113
NAME	ISS.	DATE	C/NOTE
APPROVED: M.PERREN			
CHECKED: S.BENNETT			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			