

Technical Characteristics

Approvals	UL Listed, CSA Certified, CE Marked
Integrated Communications Ports	Modbus and CANopen
Ampere Rating	54.0A
EMC Filter	No Integrated EMC Filter (C2 EMC Filter available as option)
Degree of Protection	IP20
Horsepower Rating	15HP
Motor Power Rating	11kW
Operating Temperature	14°F to 122°F (-10°C to 50°C)
Input Voltage	208/240Vac
Marketing Trade Name	Altivar 312
Input Phase	3-Phase
Output Phase	3-Phase
Type	ATV312

Shipping and Ordering

Category	22153 -
Discount Schedule	CP4B
GTIN	00785901689379
Package Quantity	1
Weight	25.82 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	ID

[document.](#)