



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	-
© COPYRIGHT 1997	-	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		G7	ECR-11-001659	24 JAN2011	SR	OH
			G8	ECR-11-002636	05 APR2011	SR	AR
			G9	ECR-11-016021	03 AUG2011	GW	OH
			G10	ECR-15-001276	29 JAN2015	GSK	MKO

NOTES

- 1 PARTS SHALL BE FREE AND CLEAN OF SHARP EDGES AND ALL OTHER FOREIGN MATERIAL NO LOOSE BURRS PERMITTED.
- 2 NBR, 70°±5° SHORE A, BLACK, ACC .TO DIN 3770
- 3 FKM, 70°±5° SHORE A, TEMPERATURE RANGE -30 °C / +200 °C
- 4 EPDM, 65°±5°SHORE A, BLACK, ELECTRICAL CONDUCTIVE, RESISTIVITY: 8.05 x 10³ OHMS PER CM
- 5 PACKAGING PN 0-1, 1000 PIECES MAX. IN A BOX


$$A - A$$


SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26.05.1999 Rösigen CHK 26.05.1999 Schweiger		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		NAME 0-Ring - -	
				SIZE A2		CAGE CODE 00779	
MATERIAL -		FINISH -		DRAWING NO C=1106053		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 of 1	
				REV G10			