


PIN RECEPTACLES

**FOR .015" - .020" DIAMETER PINS (#11 CONTACT)
AND .015" - .022" DIAMETER PINS (#05 & #21 CONTACTS)
(SEE SPECIFIC CONTACT RANGE ON PAGE 251)**

0489

0489-X-15-XX-11-XX-04-0

Press-fit in .041 mounting hole




Basic Part Number	Length A
0489-0	.102
0489-1	.199
0489-2	.299

0463

0463-0-15-XX-21-XX-04-0

Press-fit in .043 mounting hole.

Shell is Phosphor Bronze Alloy 544 (B2)




0466

0466-0-15-XX-21-XX-04-0

Press-fit in .043 mounting hole.

Shell is Phosphor Bronze Alloy 544 (B2)




7491

7491-0-15-XX-09-XX-04-0

Press-fit in .042 mounting hole


*Contact substitution not recommended



0462

0462-0-15-XX-X1-XX-04-0


Press-fit in .043 mounting hole



0560

0560-0-15-XX-11-XX-10-0


Hex press-fit in .043 plated through-hole



5552

5552-0-15-XX-05-XX-10-0


Solder mount in .040 min. mounting hole



4890

4890-X-15-XX-11-XX-04-0

Octagonal press-fit in .041 mounting hole




Basic Part Number	Length A
4890-0	.102
4890-1	.199
4890-2	.299

4994

4994-0-15-15-11-27-10-0


Compliant press-fit in .041 - .044 dia. mounting hole



4485

4485-0-51-XX-21-XX-10-0

Solder mount in .059 min. mounting hole
For wire sizes up to 22 AWG



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01** 200 μ " TIN/LEAD OVER NICKEL
- 80** 200 μ " TIN OVER NICKEL (RoHS)
- 15** 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02** 100 μ " TIN/LEAD OVER NICKEL
- 84** 100 μ " TIN OVER NICKEL (RoHS)
- 27** 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#05, #11 or #21 CONTACT (DATA ON PAGE 251)

(For alternate contact choices, see group A on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com