


Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7989R Multi-Conductor - 4-Pair UTP Cable for RGB Video



For more Information
please call

1-800-Belden1



General Description:

Category 6, 23 AWG bonded pairs solid bare copper conductors, non-plenum, polyolefin insulation, skew 10.0ns/100m nominal, rip cord, PVC jacket.

Usage (Overall)

Suitable Applications:	Category 6, UTP Based Video Applications, and KVM
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PP - Polypropylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 9.271 x 4.191 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 43.158 Kg/Km

Max. Recommended Pulling Tension: 222.410 N

Min. Bend Radius/Minor Axis: 44.450 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/UL Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (RoHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7989R Multi-Conductor - 4-Pair UTP Cable for RGB Video

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	7989P

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

Maximum Capacitance Unbalance (pF/100 m):	49.2
---	------

Nominal Velocity of Propagation:

VP (%)
70

Typical Delay Skew:

Delay Skew (ns/m)
0.100

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	74.3	72.3	70.3	20.0
4	3.8	65.3	63.3	59.5	23.0
8	5.3	60.8	58.8	53.4	24.5
10	6.0	59.3	57.3	51.3	25.0
16	7.6	56.3	54.3	46.7	25.0
20	8.5	54.8	52.8	44.3	25.0
25	9.5	53.4	51.4	41.8	24.3
31.25	10.7	51.9	49.9	39.2	23.6
62.5	15.4	47.4	45.4	30.0	21.5
100	19.8	44.3	42.3	22.5	20.1
155	25.2	41.5	39.5	14.3	18.8
200	29.0	39.8	37.8	8.8	18.0
250	32.8	38.3	36.3	3.5	17.3

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	67.8	64.8
4	100 ± 15	55.7	52.7
8	100 ± 15	49.7	46.7
10	100 ± 15	47.8	44.8
16	100 ± 15	43.7	40.7
20	100 ± 15	41.7	38.7
25	100 ± 15	39.8	36.8

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

7989R Multi-Conductor - 4-Pair UTP Cable for RGB Video

31.25	100 ± 15	37.9	34.9
62.5	100 ± 15	31.8	28.8
100	100 ± 15	27.8	24.8
155	100 ± 22	23.9	20.9
200	100 ± 22	21.8	18.7
250	100 ± 32	19.8	16.8

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7989R 0131000	305 MT	14.515 KG	BLUE, DARK	C	4 PR #23 PP PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 03-11-2014

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7989R 0131000](#)